

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366275

Luminaire Tested: **FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL84
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3681.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366275

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P366275

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129496
5°	128949
10°	122496
15°	111269
20°	96824
25°	82319
30°	64754
35°	36947
40°	16624
45°	6996
50°	2210
55°	667
60°	459
65°	362
70°	335
75°	443
80°	220
85°	439



TEST NUMBER: P366275

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.9	12.0
10°-20°	1094.5	29.7
20°-30°	1240.3	33.7
30°-40°	719.0	19.5
40°-50°	159.4	4.3
50°-60°	17.5	0.5
60°-70°	5.7	0.2
70°-80°	3.7	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2774.7	75.4
0°-40°	3493.7	94.9
0°-60°	3670.6	99.7
0°-90°	3681.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3681.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4741	
5°	4703	440
15°	3935	1095
25°	2731	1240
35°	1108	719
45°	181	159
55°	14	17
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P366275

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL84

CANDELA DISTRIBUTION (FULL):

0°	
0°	4740.8
2.5°	4745.0
5°	4702.8
7.5°	4600.3
10°	4416.4
12.5°	4193.1
15°	3934.7
17.5°	3662.3
20°	3330.9
22.5°	3031.8
25°	2731.3
27.5°	2411.1
30°	2053.0
32.5°	1630.3
35°	1108.0
37.5°	712.0
40°	466.2
42.5°	304.7
45°	181.1
47.5°	101.1
50°	52.0
52.5°	23.9
55°	14.0
57.5°	11.2
60°	8.4
62.5°	7.0
65°	5.6
67.5°	4.2
70°	4.2
72.5°	4.2
75°	4.2
77.5°	2.8
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)