

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366276

Luminaire Tested: **FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL85
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3668.0 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366276

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL85

Luminous Intensity Polar Plot





TEST NUMBER: P366276

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129037
5°	128494
10°	122063
15°	110876
20°	96481
25°	82026
30°	64526
35°	36814
40°	16566
45°	6973
50°	2201
55°	667
60°	459
65°	362
70°	335
75°	443
80°	220
85°	439



TEST NUMBER: P366276

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.3	12.0
10°-20°	1090.6	29.7
20°-30°	1235.9	33.7
30°-40°	716.5	19.5
40°-50°	158.9	4.3
50°-60°	17.4	0.5
60°-70°	5.7	0.2
70°-80°	3.7	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2764.9	75.4
0°-40°	3481.4	94.9
0°-60°	3657.7	99.7
0°-90°	3668.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3668.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4724	
5°	4686	438
15°	3921	1091
25°	2722	1236
35°	1104	716
45°	180	159
55°	14	17
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P366276

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BL85

CANDELA DISTRIBUTION (FULL):

0°	
0°	4724.0
2.5°	4728.2
5°	4686.2
7.5°	4584.1
10°	4400.8
12.5°	4178.3
15°	3920.8
17.5°	3649.4
20°	3319.1
22.5°	3021.1
25°	2721.6
27.5°	2402.6
30°	2045.8
32.5°	1624.6
35°	1104.0
37.5°	709.4
40°	464.6
42.5°	303.6
45°	180.5
47.5°	100.7
50°	51.8
52.5°	23.8
55°	14.0
57.5°	11.2
60°	8.4
62.5°	7.0
65°	5.6
67.5°	4.2
70°	4.2
72.5°	4.2
75°	4.2
77.5°	2.8
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)