

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366283

Luminaire Tested: **FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-31)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3011.0 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.19
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366283

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81

Luminous Intensity Polar Plot





TEST NUMBER: P366283

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	51	46	68	57	50	45	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113346
5°	121146
10°	129694
15°	132540
20°	129710
25°	122843
30°	111831
35°	98100
40°	82842
45°	66994
50°	51631
55°	37700
60°	25949
65°	17129
70°	11179
75°	8161
80°	6969
85°	8051



TEST NUMBER: P366283

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	5.4
10°-20°	500.7	16.6
20°-30°	709.4	23.6
30°-40°	699.7	23.2
40°-50°	512.9	17.0
50°-60°	275.0	9.1
60°-70°	105.7	3.5
70°-80°	33.7	1.1
80°-90°	9.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1374.2	45.6
0°-40°	2073.9	68.9
0°-60°	2861.7	95.0
0°-90°	3011.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3011.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1583	
5°	1686	164
15°	1788	501
25°	1555	709
35°	1122	700
45°	662	513
55°	302	275
65°	101	106
75°	30	34
85°	10	10
90°	0	



TEST NUMBER: P366283

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-WMH-BTR81

CANDELA DISTRIBUTION (FULL):

	0°
0°	1583.0
2.5°	1619.5
5°	1685.5
7.5°	1747.3
10°	1783.8
12.5°	1796.5
15°	1788.0
17.5°	1754.3
20°	1702.3
22.5°	1636.3
25°	1554.9
27.5°	1453.7
30°	1352.6
32.5°	1243.1
35°	1122.3
37.5°	1007.1
40°	886.3
42.5°	775.3
45°	661.6
47.5°	560.4
50°	463.5
52.5°	376.4
55°	302.0
57.5°	236.0
60°	181.2
62.5°	136.2
65°	101.1
67.5°	74.4
70°	53.4
72.5°	40.7
75°	29.5
77.5°	22.5
80°	16.9
82.5°	12.6
85°	9.8
87.5°	5.6
90°	0.0

(END OF REPORT)