

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366250

Luminaire Tested: **FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BTR85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366250  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BTR85  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2912.0 lumens  
Efficiency: N/A  
Efficacy: 71.7 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366250

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BTR85

### Luminous Intensity Polar Plot





TEST NUMBER: P366250

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BTR85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	301071
5°	296112
10°	282145
15°	257824
20°	221094
25°	177403
30°	124382
35°	57463
40°	18451
45°	5954
50°	2763
55°	2447
60°	2434
65°	2219
70°	2198
75°	2517
80°	3216
85°	5340



TEST NUMBER: P366250

CATALOG NUMBER: FLD6BX40D010-FEUGB35-8027-F6LBXVM1-WMH-BTR85

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	386.4	13.3
10°-20°	962.5	33.1
20°-30°	1010.8	34.7
30°-40°	448.5	15.4
40°-50°	58.0	2.0
50°-60°	18.1	0.6
60°-70°	12.8	0.4
70°-80°	9.3	0.3
80°-90°	5.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2359.6	81.0
0°-40°	2808.1	96.4
0°-60°	2884.2	99.0
0°-90°	2912.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2912.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4205	
5°	4120	386
15°	3478	962
25°	2246	1011
35°	657	449
45°	59	58
55°	20	18
65°	13	13
75°	9	9
85°	6	6
90°	0	



TEST NUMBER: P366250

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8027-F6LBXVM1-WMH-BTR85

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4204.8
2.5°	4178.6
5°	4119.8
7.5°	4040.1
10°	3880.6
12.5°	3701.6
15°	3478.1
17.5°	3210.1
20°	2901.6
22.5°	2577.5
25°	2245.5
27.5°	1873.0
30°	1504.4
32.5°	1105.8
35°	657.4
37.5°	350.3
40°	197.4
42.5°	108.5
45°	58.8
47.5°	30.1
50°	24.8
52.5°	22.2
55°	19.6
57.5°	18.3
60°	17.0
62.5°	14.4
65°	13.1
67.5°	10.5
70°	10.5
72.5°	9.1
75°	9.1
77.5°	7.8
80°	7.8
82.5°	6.5
85°	6.5
87.5°	3.9
90°	0.0

(END OF REPORT)