

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364859

Luminaire Tested: **FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL89BW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364859
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL89BW
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC OPAL SMOOTH, CLEAR 0.125", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2927.0 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364859

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL89BW

Luminous Intensity Polar Plot





TEST NUMBER: P364859

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL89BW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	69	63		72	67	62		70	65	61	59
4	83	71	62	55	80	69	61	55	67	59	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	43	36	63	51	42	36	49	41	36		48	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		44	37	32		42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29		40	34	29		39	33	29	27
10	53	40	32	26	52	39	32	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28536
5°	28530
10°	28230
15°	28058
20°	27975
25°	27680
30°	27488
35°	27217
40°	26825
45°	26539
50°	26117
55°	25621
60°	24813
65°	23759
70°	22218
75°	19778
80°	15856
85°	9778



TEST NUMBER: P364859

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL89BW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.6	3.4
10°-20°	280.6	9.6
20°-30°	424.0	14.5
30°-40°	509.9	17.4
40°-50°	529.6	18.1
50°-60°	480.2	16.4
60°-70°	363.4	12.4
70°-80°	198.5	6.8
80°-90°	42.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	803.1	27.4
0°-40°	1313.0	44.9
0°-60°	2322.8	79.4
0°-90°	2927.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2927.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1045	
5°	1040	99
15°	992	281
25°	918	424
35°	816	510
45°	687	530
55°	538	480
65°	368	363
75°	187	198
85°	31	42
90°	0	



TEST NUMBER: P364859

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL89BW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1044.7
2.5°	1040.5
5°	1040.5
7.5°	1031.9
10°	1017.8
12.5°	1010.7
15°	992.2
17.5°	978.0
20°	962.4
22.5°	943.9
25°	918.4
27.5°	895.7
30°	871.5
32.5°	844.6
35°	816.2
37.5°	783.5
40°	752.3
42.5°	721.1
45°	687.0
47.5°	651.5
50°	614.6
52.5°	577.7
55°	538.0
57.5°	496.8
60°	454.2
62.5°	411.6
65°	367.6
67.5°	323.6
70°	278.2
72.5°	232.8
75°	187.4
77.5°	143.4
80°	100.8
82.5°	63.9
85°	31.2
87.5°	9.9
90°	0.0

(END OF REPORT)