

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365537

Luminaire Tested: **FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365537  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3169.0 lumens  
Efficiency: N/A  
Efficacy: 78.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365537

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL84

### Luminous Intensity Polar Plot





TEST NUMBER: P365537

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56	65	60	56	64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	70208
5°	68777
10°	65334
15°	61122
20°	57026
25°	52321
30°	44681
35°	34063
40°	25085
45°	19041
50°	15502
55°	13639
60°	12183
65°	10768
70°	9129
75°	7124
80°	4766
85°	2163



TEST NUMBER: P365537

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	234.5	7.4
10°-20°	606.5	19.1
20°-30°	788.3	24.9
30°-40°	642.3	20.3
40°-50°	389.9	12.3
50°-60°	258.0	8.1
60°-70°	165.5	5.2
70°-80°	73.1	2.3
80°-90°	10.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1629.3	51.4
0°-40°	2271.7	71.7
0°-60°	2919.6	92.1
0°-90°	3169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3169.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2570	
5°	2508	235
15°	2161	607
25°	1736	788
35°	1022	642
45°	493	390
55°	286	258
65°	167	166
75°	68	73
85°	7	11
90°	0	



TEST NUMBER: P365537

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2570.3
2.5°	2553.8
5°	2508.3
7.5°	2439.5
10°	2355.5
12.5°	2261.9
15°	2161.4
17.5°	2058.2
20°	1961.8
22.5°	1857.2
25°	1736.0
27.5°	1592.8
30°	1416.6
32.5°	1218.4
35°	1021.5
37.5°	846.7
40°	703.5
42.5°	583.7
45°	492.9
47.5°	421.3
50°	364.8
52.5°	322.1
55°	286.4
57.5°	253.3
60°	223.0
62.5°	194.1
65°	166.6
67.5°	140.4
70°	114.3
72.5°	89.5
75°	67.5
77.5°	48.2
80°	30.3
82.5°	16.5
85°	6.9
87.5°	1.4
90°	0.0

(END OF REPORT)