

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365538

Luminaire Tested: **FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365538  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL85  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3158.1 lumens  
Efficiency: N/A  
Efficacy: 77.8 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365538

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL85

### Luminous Intensity Polar Plot





TEST NUMBER: P365538

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	73	68	76	71	67	74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59
6	80	69	62	57	78	68	62	57	67	61	56	65	60	56	64	59	55	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	69908
5°	68365
10°	64840
15°	60774
20°	56706
25°	52159
30°	44684
35°	34019
40°	24989
45°	18932
50°	15502
55°	13639
60°	12183
65°	10677
70°	9129
75°	7124
80°	4766
85°	2163



TEST NUMBER: P365538

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL85

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	233.0	7.4
10°-20°	603.3	19.1
20°-30°	786.2	24.9
30°-40°	641.0	20.3
40°-50°	388.0	12.3
50°-60°	257.7	8.2
60°-70°	164.8	5.2
70°-80°	73.1	2.3
80°-90°	10.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1622.5	51.4
0°-40°	2263.5	71.7
0°-60°	2909.3	92.1
0°-90°	3158.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3158.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2559	
5°	2493	233
15°	2149	603
25°	1731	786
35°	1020	641
45°	490	388
55°	286	258
65°	165	165
75°	68	73
85°	7	11
90°	0	



TEST NUMBER: P365538

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-MW-BL85

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2559.3
2.5°	2540.1
5°	2493.3
7.5°	2423.1
10°	2337.7
12.5°	2244.1
15°	2149.1
17.5°	2054.1
20°	1950.8
22.5°	1851.7
25°	1730.6
27.5°	1590.1
30°	1416.7
32.5°	1218.4
35°	1020.2
37.5°	841.2
40°	700.8
42.5°	581.0
45°	490.1
47.5°	418.5
50°	364.8
52.5°	320.8
55°	286.4
57.5°	253.3
60°	223.0
62.5°	194.1
65°	165.2
67.5°	139.1
70°	114.3
72.5°	89.5
75°	67.5
77.5°	48.2
80°	30.3
82.5°	16.5
85°	6.9
87.5°	1.4
90°	0.0

(END OF REPORT)