

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366294

Luminaire Tested: **FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BL85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366294  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BL85  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.187", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3706.9 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366294

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BL85

### Luminous Intensity Polar Plot





TEST NUMBER: P366294

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BL85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	130409
5°	129862
10°	123362
15°	112055
20°	97507
25°	82901
30°	65211
35°	37207
40°	16741
45°	7046
50°	2222
55°	671
60°	464
65°	368
70°	335
75°	443
80°	220
85°	439



TEST NUMBER: P366294

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BL85

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	443.0	12.0
10°-20°	1102.2	29.7
20°-30°	1249.0	33.7
30°-40°	724.1	19.5
40°-50°	160.6	4.3
50°-60°	17.6	0.5
60°-70°	5.8	0.2
70°-80°	3.7	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2794.3	75.4
0°-40°	3518.4	94.9
0°-60°	3696.5	99.7
0°-90°	3706.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3706.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4774	
5°	4736	443
15°	3962	1102
25°	2751	1249
35°	1116	724
45°	182	161
55°	14	18
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P366294

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BL85

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4774.2
2.5°	4778.5
5°	4736.1
7.5°	4632.8
10°	4447.6
12.5°	4222.7
15°	3962.5
17.5°	3688.2
20°	3354.4
22.5°	3053.2
25°	2750.6
27.5°	2428.1
30°	2067.5
32.5°	1641.9
35°	1115.8
37.5°	717.0
40°	469.5
42.5°	306.9
45°	182.4
47.5°	101.8
50°	52.3
52.5°	24.0
55°	14.1
57.5°	11.3
60°	8.5
62.5°	7.1
65°	5.7
67.5°	4.2
70°	4.2
72.5°	4.2
75°	4.2
77.5°	2.8
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)