

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366259

Luminaire Tested: **FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366259
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3551.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366259

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P366259

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124921
5°	124397
10°	118169
15°	107341
20°	93402
25°	79410
30°	62467
35°	35640
40°	16035
45°	6752
50°	2129
55°	643
60°	443
65°	349
70°	327
75°	433
80°	220
85°	439



TEST NUMBER: P366259

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	424.4	12.0
10°-20°	1055.9	29.7
20°-30°	1196.5	33.7
30°-40°	693.6	19.5
40°-50°	153.8	4.3
50°-60°	16.8	0.5
60°-70°	5.5	0.2
70°-80°	3.6	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2676.7	75.4
0°-40°	3370.3	94.9
0°-60°	3540.9	99.7
0°-90°	3551.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3551.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4573	
5°	4537	424
15°	3796	1056
25°	2635	1196
35°	1069	694
45°	175	154
55°	14	17
65°	5	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P366259

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	4573.3
2.5°	4577.4
5°	4536.8
7.5°	4437.9
10°	4260.4
12.5°	4045.0
15°	3795.8
17.5°	3532.9
20°	3213.2
22.5°	2924.7
25°	2634.8
27.5°	2325.9
30°	1980.5
32.5°	1572.8
35°	1068.8
37.5°	686.8
40°	449.7
42.5°	294.0
45°	174.8
47.5°	97.5
50°	50.1
52.5°	23.0
55°	13.5
57.5°	10.8
60°	8.1
62.5°	6.8
65°	5.4
67.5°	4.1
70°	4.1
72.5°	4.1
75°	4.1
77.5°	2.7
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)