

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366264

Luminaire Tested: **FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BTR80**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-29)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BTR80
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, PATTERN 12 0.125", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3120.0 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366264

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BTR80

Luminous Intensity Polar Plot





TEST NUMBER: P366264

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BTR80

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	100	92	86	82	97	91	85	81	88	84	80	85	82	79	83	80	77	76
4	94	85	79	74	92	84	78	73	82	77	72	79	75	72	78	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	79	68	61	57	77	67	61	57	66	60	56	65	60	56	64	59	56	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47
10	67	56	50	46	66	56	50	46	55	49	45	54	49	45	53	49	45	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	222367
5°	217775
10°	205876
15°	188166
20°	165310
25°	140508
30°	114948
35°	90487
40°	67420
45°	47815
50°	33730
55°	24230
60°	17342
65°	12588
70°	9798
75°	7995
80°	6804
85°	6819



TEST NUMBER: P366264

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BTR80

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.0	9.1
10°-20°	706.3	22.6
20°-30°	812.5	26.0
30°-40°	648.3	20.8
40°-50°	373.8	12.0
50°-60°	178.1	5.7
60°-70°	77.1	2.5
70°-80°	31.6	1.0
80°-90°	9.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1801.8	57.7
0°-40°	2450.1	78.5
0°-60°	3002.0	96.2
0°-90°	3120.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3120.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3106	
5°	3030	283
15°	2538	706
25°	1778	812
35°	1035	648
45°	472	374
55°	194	178
65°	74	77
75°	29	32
85°	8	9
90°	0	



TEST NUMBER: P366264

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8030-F6LBXVM1-WMH-BTR80

CANDELA DISTRIBUTION (FULL):

0°	
0°	3105.6
2.5°	3086.3
5°	3029.9
7.5°	2945.9
10°	2831.6
12.5°	2698.1
15°	2538.4
17.5°	2365.0
20°	2169.5
22.5°	1972.6
25°	1778.5
27.5°	1581.7
30°	1390.3
32.5°	1215.5
35°	1035.2
37.5°	874.1
40°	721.3
42.5°	590.6
45°	472.2
47.5°	378.6
50°	302.8
52.5°	242.3
55°	194.1
57.5°	152.8
60°	121.1
62.5°	95.0
65°	74.3
67.5°	59.2
70°	46.8
72.5°	37.2
75°	28.9
77.5°	22.0
80°	16.5
82.5°	12.4
85°	8.3
87.5°	5.5
90°	0.0

(END OF REPORT)