

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364883

Luminaire Tested: **FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BTR86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364883  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BTR86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3163.0 lumens  
Efficiency: N/A  
Efficacy: 77.9 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364883

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BTR86

### Luminous Intensity Polar Plot





TEST NUMBER: P364883

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BTR86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	355009
5°	346914
10°	319821
15°	283264
20°	239823
25°	189996
30°	133518
35°	55610
40°	19077
45°	5093
50°	2807
55°	2622
60°	2406
65°	2372
70°	2345
75°	2711
80°	3464
85°	5751



TEST NUMBER: P364883

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BTR86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	447.3	14.1
10°-20°	1060.1	33.5
20°-30°	1088.3	34.4
30°-40°	460.8	14.6
40°-50°	56.7	1.8
50°-60°	18.8	0.6
60°-70°	13.9	0.4
70°-80°	10.7	0.3
80°-90°	6.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2595.7	82.1
0°-40°	3056.5	96.6
0°-60°	3132.0	99.0
0°-90°	3163.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3163.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4958	
5°	4827	447
15°	3821	1060
25°	2405	1088
35°	636	461
45°	50	57
55°	21	19
65°	14	14
75°	10	11
85°	7	6
90°	0	



TEST NUMBER: P364883

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BTR86

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4958.1
2.5°	4925.9
5°	4826.6
7.5°	4656.1
10°	4398.8
12.5°	4124.7
15°	3821.3
17.5°	3495.5
20°	3147.4
22.5°	2776.9
25°	2404.9
27.5°	2020.4
30°	1614.9
32.5°	1138.1
35°	636.2
37.5°	364.9
40°	204.1
42.5°	107.7
45°	50.3
47.5°	29.4
50°	25.2
52.5°	22.4
55°	21.0
57.5°	19.6
60°	16.8
62.5°	15.4
65°	14.0
67.5°	12.6
70°	11.2
72.5°	11.2
75°	9.8
77.5°	9.8
80°	8.4
82.5°	8.4
85°	7.0
87.5°	4.2
90°	0.0

(END OF REPORT)