

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364850

Luminaire Tested: **FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BTR89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364850  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BTR89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR 0.125", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3330.0 lumens  
Efficiency: N/A  
Efficacy: 82.0 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364850

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BTR89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P364850

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BTR89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	373132
5°	364466
10°	334988
15°	298127
20°	252517
25°	200804
30°	141182
35°	58914
40°	20348
45°	5266
50°	2662
55°	2459
60°	2420
65°	2372
70°	2345
75°	3098
80°	3464
85°	5751



TEST NUMBER: P364850

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BTR89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	469.4	14.1
10°-20°	1114.1	33.5
20°-30°	1149.6	34.5
30°-40°	489.0	14.7
40°-50°	58.7	1.8
50°-60°	17.8	0.5
60°-70°	13.9	0.4
70°-80°	11.1	0.3
80°-90°	6.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2733.1	82.1
0°-40°	3222.0	96.8
0°-60°	3298.5	99.1
0°-90°	3330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3330.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5211	
5°	5071	469
15°	4022	1114
25°	2542	1150
35°	674	489
45°	52	59
55°	20	18
65°	14	14
75°	11	11
85°	7	6
90°	0	



TEST NUMBER: P364850

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-LI-BTR89BV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5211.2
2.5°	5177.5
5°	5070.8
7.5°	4885.4
10°	4607.4
12.5°	4333.5
15°	4021.8
17.5°	3670.7
20°	3314.0
22.5°	2941.9
25°	2541.7
27.5°	2128.8
30°	1707.6
32.5°	1210.5
35°	674.0
37.5°	387.6
40°	217.7
42.5°	112.3
45°	52.0
47.5°	28.1
50°	23.9
52.5°	21.1
55°	19.7
57.5°	18.3
60°	16.9
62.5°	15.4
65°	14.0
67.5°	12.6
70°	11.2
72.5°	11.2
75°	11.2
77.5°	9.8
80°	8.4
82.5°	8.4
85°	7.0
87.5°	4.2
90°	0.0

(END OF REPORT)