

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365567

Luminaire Tested: **FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365567
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-17)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2400.0 lumens
Efficiency: N/A
Efficacy: 59.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365567

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P365567

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	98	93	89	94	91	87		91	88	85		88	86	84	82
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	72	69	68
5	87	78	71	66	86	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	66	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	51	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		53	48	45		53	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169761
5°	166679
10°	158289
15°	147951
20°	133886
25°	111190
30°	79777
35°	54753
40°	40304
45°	32565
50°	28316
55°	24892
60°	21524
65°	18332
70°	14403
75°	10098
80°	6391
85°	6901



TEST NUMBER: P365567

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.9	9.0
10°-20°	556.9	23.2
20°-30°	631.7	26.3
30°-40°	404.9	16.9
40°-50°	253.8	10.6
50°-60°	179.0	7.5
60°-70°	107.5	4.5
70°-80°	41.0	1.7
80°-90°	8.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1405.6	58.6
0°-40°	1810.4	75.4
0°-60°	2243.2	93.5
0°-90°	2400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2400.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2371	
5°	2319	217
15°	1996	557
25°	1407	632
35°	626	405
45°	322	254
55°	199	179
65°	108	108
75°	36	41
85°	8	8
90°	0	



TEST NUMBER: P365567

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR86

CANDELA DISTRIBUTION (FULL):

0°	
0°	2370.9
2.5°	2363.9
5°	2319.0
7.5°	2258.6
10°	2177.1
12.5°	2088.6
15°	1995.9
17.5°	1890.6
20°	1757.1
22.5°	1601.2
25°	1407.4
27.5°	1184.1
30°	964.9
32.5°	779.5
35°	626.4
37.5°	515.5
40°	431.2
42.5°	369.4
45°	321.6
47.5°	286.5
50°	254.2
52.5°	226.1
55°	199.4
57.5°	174.2
60°	150.3
62.5°	129.2
65°	108.2
67.5°	88.5
70°	68.8
72.5°	52.0
75°	36.5
77.5°	25.3
80°	15.5
82.5°	9.8
85°	8.4
87.5°	4.2
90°	0.0

(END OF REPORT)