

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365568

Luminaire Tested: **FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2444.0 lumens
Efficiency: N/A
Efficacy: 60.2 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365568

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P365568

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	106	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	84	77	72	91	82	76	71	80	75	71		78	73	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	61
6	82	72	65	60	80	71	64	60	69	63	59		68	63	59		66	62	58	57
7	77	67	60	55	76	66	60	55	65	59	55		63	58	54		62	58	54	52
8	73	62	56	51	72	62	55	51	61	55	51		60	54	50		59	54	50	49
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168952
5°	166169
10°	157867
15°	147514
20°	134610
25°	112699
30°	82034
35°	56755
40°	41510
45°	33446
50°	28962
55°	25616
60°	22340
65°	19043
70°	15597
75°	11675
80°	8123
85°	6901



TEST NUMBER: P365568

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.0	8.8
10°-20°	555.8	22.7
20°-30°	641.6	26.3
30°-40°	418.4	17.1
40°-50°	259.7	10.6
50°-60°	184.5	7.5
60°-70°	112.1	4.6
70°-80°	46.4	1.9
80°-90°	9.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1413.3	57.8
0°-40°	1831.7	74.9
0°-60°	2275.9	93.1
0°-90°	2444.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2444.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2360	
5°	2312	216
15°	1990	556
25°	1426	642
35°	649	418
45°	330	260
55°	205	184
65°	112	112
75°	42	46
85°	8	10
90°	0	



TEST NUMBER: P365568

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8035-F6LBXVM1-MW-BTR87

CANDELA DISTRIBUTION (FULL):

	0°
0°	2359.6
2.5°	2347.0
5°	2311.9
7.5°	2245.8
10°	2171.3
12.5°	2082.8
15°	1990.0
17.5°	1883.2
20°	1766.6
22.5°	1616.2
25°	1426.5
27.5°	1214.2
30°	992.2
32.5°	806.7
35°	649.3
37.5°	532.6
40°	444.1
42.5°	378.0
45°	330.3
47.5°	290.9
50°	260.0
52.5°	231.9
55°	205.2
57.5°	181.3
60°	156.0
62.5°	133.5
65°	112.4
67.5°	92.8
70°	74.5
72.5°	57.6
75°	42.2
77.5°	29.5
80°	19.7
82.5°	12.6
85°	8.4
87.5°	4.2
90°	0.0

(END OF REPORT)