

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366313

Luminaire Tested: **FLD6BX40D010-FEU6B35-8050-F6LBXVM1-WMH-BL86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366313  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-WMH-BL86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 4000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3749.0 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366313

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-WMH-BL86

### Luminous Intensity Polar Plot





TEST NUMBER: P366313

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-WMH-BL86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	131886
5°	131332
10°	124759
15°	113325
20°	98611
25°	83838
30°	65949
35°	37627
40°	16930
45°	7127
50°	2248
55°	681
60°	470
65°	368
70°	343
75°	454
80°	220
85°	439



TEST NUMBER: P366313

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-WMH-BL86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	448.0	12.0
10°-20°	1114.7	29.7
20°-30°	1263.2	33.7
30°-40°	732.3	19.5
40°-50°	162.4	4.3
50°-60°	17.8	0.5
60°-70°	5.8	0.2
70°-80°	3.8	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2825.9	75.4
0°-40°	3558.2	94.9
0°-60°	3738.4	99.7
0°-90°	3749.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3749.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4828	
5°	4790	448
15°	4007	1115
25°	2782	1263
35°	1128	732
45°	184	162
55°	14	18
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P366313

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-WMH-BL86

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4828.3
2.5°	4832.6
5°	4789.7
7.5°	4685.3
10°	4498.0
12.5°	4270.6
15°	4007.4
17.5°	3729.9
20°	3392.4
22.5°	3087.8
25°	2781.7
27.5°	2455.6
30°	2090.9
32.5°	1660.5
35°	1128.4
37.5°	725.1
40°	474.8
42.5°	310.4
45°	184.5
47.5°	103.0
50°	52.9
52.5°	24.3
55°	14.3
57.5°	11.4
60°	8.6
62.5°	7.2
65°	5.7
67.5°	4.3
70°	4.3
72.5°	4.3
75°	4.3
77.5°	2.9
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)