

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364899

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3699.9 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364899

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P364899

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	415276
5°	405815
10°	374118
15°	331358
20°	280535
25°	222254
30°	156188
35°	65050
40°	22321
45°	5964
50°	3275
55°	3058
60°	2807
65°	2779
70°	2742
75°	3154
80°	4041
85°	6737



TEST NUMBER: P364899

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	523.2	14.1
10°-20°	1240.1	33.5
20°-30°	1273.1	34.4
30°-40°	539.1	14.6
40°-50°	66.3	1.8
50°-60°	21.9	0.6
60°-70°	16.2	0.4
70°-80°	12.5	0.3
80°-90°	7.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3036.4	82.1
0°-40°	3575.5	96.6
0°-60°	3663.7	99.0
0°-90°	3699.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3699.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5800	
5°	5646	523
15°	4470	1240
25°	2813	1273
35°	744	539
45°	59	66
55°	24	22
65°	16	16
75°	11	13
85°	8	8
90°	0	



TEST NUMBER: P364899

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR84

CANDELA DISTRIBUTION (FULL):

0°	
0°	5799.8
2.5°	5762.2
5°	5646.1
7.5°	5446.5
10°	5145.6
12.5°	4825.0
15°	4470.1
17.5°	4089.0
20°	3681.7
22.5°	3248.3
25°	2813.2
27.5°	2363.4
30°	1889.1
32.5°	1331.4
35°	744.2
37.5°	426.9
40°	238.8
42.5°	125.9
45°	58.9
47.5°	34.3
50°	29.4
52.5°	26.2
55°	24.5
57.5°	22.9
60°	19.6
62.5°	18.0
65°	16.4
67.5°	14.7
70°	13.1
72.5°	13.1
75°	11.4
77.5°	11.4
80°	9.8
82.5°	9.8
85°	8.2
87.5°	4.9
90°	0.0

(END OF REPORT)