

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364856

Luminaire Tested: **FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL87
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.375", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3555.0 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364856

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL87

Luminous Intensity Polar Plot





TEST NUMBER: P364856

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136776
5°	134175
10°	123908
15°	110415
20°	94298
25°	79193
30°	62167
35°	32215
40°	15386
45°	6057
50°	1594
55°	448
60°	295
65°	259
70°	216
75°	285
80°	204
85°	407



TEST NUMBER: P364856

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	453.8	12.8
10°-20°	1085.2	30.5
20°-30°	1198.1	33.7
30°-40°	659.3	18.5
40°-50°	139.4	3.9
50°-60°	11.8	0.3
60°-70°	3.6	0.1
70°-80°	2.6	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2737.0	77.0
0°-40°	3396.3	95.5
0°-60°	3547.5	99.8
0°-90°	3555.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3555.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5007	
5°	4893	454
15°	3904	1085
25°	2628	1198
35°	966	659
45°	157	139
55°	9	12
65°	4	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P364856

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-LI-BL87

CANDELA DISTRIBUTION (FULL):

	0°
0°	5007.3
2.5°	5004.6
5°	4893.4
7.5°	4721.9
10°	4467.3
12.5°	4214.1
15°	3904.5
17.5°	3589.7
20°	3244.0
22.5°	2941.1
25°	2627.6
27.5°	2324.8
30°	1971.0
32.5°	1504.7
35°	966.1
37.5°	651.2
40°	431.5
42.5°	269.3
45°	156.8
47.5°	80.4
50°	37.5
52.5°	16.1
55°	9.4
57.5°	6.7
60°	5.4
62.5°	4.0
65°	4.0
67.5°	2.7
70°	2.7
72.5°	4.0
75°	2.7
77.5°	1.3
80°	1.3
82.5°	1.3
85°	1.3
87.5°	1.3
90°	0.0

(END OF REPORT)