

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365575

Luminaire Tested: **FLD6BX40D010-FEU6B35-8040-F6LBXVM1-MW-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-38)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-MW-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3215.0 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365575

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-MW-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P365575

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-MW-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		83	78	75		80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71353
5°	69681
10°	66080
15°	61874
20°	57785
25°	53198
30°	45469
35°	34586
40°	25349
45°	19295
50°	15736
55°	13853
60°	12325
65°	10820
70°	9176
75°	7187
80°	4908
85°	2225



TEST NUMBER: P365575

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-MW-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.5	7.4
10°-20°	615.0	19.1
20°-30°	800.7	24.9
30°-40°	653.5	20.3
40°-50°	395.1	12.3
50°-60°	261.7	8.1
60°-70°	166.5	5.2
70°-80°	73.8	2.3
80°-90°	11.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1653.3	51.4
0°-40°	2306.8	71.8
0°-60°	2963.5	92.2
0°-90°	3215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3215.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2612	
5°	2541	238
15°	2188	615
25°	1765	801
35°	1037	653
45°	500	395
55°	291	262
65°	167	167
75°	68	74
85°	7	11
90°	0	



TEST NUMBER: P365575

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-MW-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	2612.2
2.5°	2585.3
5°	2541.3
7.5°	2471.8
10°	2382.4
12.5°	2291.6
15°	2188.0
17.5°	2094.3
20°	1987.9
22.5°	1885.7
25°	1765.1
27.5°	1617.6
30°	1441.6
32.5°	1244.4
35°	1037.2
37.5°	861.3
40°	710.9
42.5°	591.7
45°	499.5
47.5°	427.1
50°	370.3
52.5°	326.4
55°	290.9
57.5°	256.8
60°	225.6
62.5°	195.8
65°	167.4
67.5°	140.5
70°	114.9
72.5°	90.8
75°	68.1
77.5°	48.2
80°	31.2
82.5°	17.0
85°	7.1
87.5°	1.4
90°	0.0

(END OF REPORT)