

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366347

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8030-F6LBXVM1-WMH-BL84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-47)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8030-F6LBXVM1-WMH-BL84
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, WARM HAZE REFLECTOR, BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4482.0 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366347

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8030-F6LBXVM1-WMH-BL84

Luminous Intensity Polar Plot





TEST NUMBER: P366347

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8030-F6LBXVM1-WMH-BL84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	88	85		88	86	84	82
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	76	92	85	79	75	83	78	75		81	77	74		80	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		76	72	69	68
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72	68	65	63
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68	64	61	60
9	77	68	62	58	76	67	62	58	66	62	58		66	61	58		65	61	58	56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62	58	55	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157675
5°	157010
10°	149151
15°	135481
20°	117892
25°	100230
30°	78846
35°	44983
40°	20243
45°	8522
50°	2690
55°	814
60°	563
65°	440
70°	407
75°	538
80°	267
85°	533



TEST NUMBER: P366347

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8030-F6LBXVM1-WMH-BL84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	535.6	12.0
10°-20°	1332.7	29.7
20°-30°	1510.2	33.7
30°-40°	875.5	19.5
40°-50°	194.1	4.3
50°-60°	21.3	0.5
60°-70°	6.9	0.2
70°-80°	4.5	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3378.5	75.4
0°-40°	4253.9	94.9
0°-60°	4469.4	99.7
0°-90°	4482.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4482.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5772	
5°	5726	536
15°	4791	1333
25°	3326	1510
35°	1349	875
45°	221	194
55°	17	21
65°	7	7
75°	5	4
85°	2	1
90°	0	



TEST NUMBER: P366347

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8030-F6LBXVM1-WMH-BL84

CANDELA DISTRIBUTION (FULL):

0°	
0°	5772.4
2.5°	5777.5
5°	5726.2
7.5°	5601.4
10°	5377.4
12.5°	5105.5
15°	4790.9
17.5°	4459.2
20°	4055.7
22.5°	3691.5
25°	3325.6
27.5°	2935.8
30°	2499.8
32.5°	1985.1
35°	1349.0
37.5°	866.9
40°	567.7
42.5°	371.0
45°	220.6
47.5°	123.1
50°	63.3
52.5°	29.1
55°	17.1
57.5°	13.7
60°	10.3
62.5°	8.5
65°	6.8
67.5°	5.1
70°	5.1
72.5°	5.1
75°	5.1
77.5°	3.4
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

(END OF REPORT)