

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366306

Luminaire Tested: **FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3095.0 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366306

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P366306

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	319989
5°	314721
10°	299878
15°	274020
20°	234992
25°	188551
30°	132203
35°	61082
40°	19610
45°	6329
50°	2941
55°	2597
60°	2592
65°	2355
70°	2324
75°	2683
80°	3422
85°	5669



TEST NUMBER: P366306

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	410.7	13.3
10°-20°	1022.9	33.1
20°-30°	1074.3	34.7
30°-40°	476.7	15.4
40°-50°	61.6	2.0
50°-60°	19.2	0.6
60°-70°	13.6	0.4
70°-80°	9.9	0.3
80°-90°	6.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2507.9	81.0
0°-40°	2984.6	96.4
0°-60°	3065.5	99.0
0°-90°	3095.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3095.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4469	
5°	4379	411
15°	3697	1023
25°	2387	1074
35°	699	477
45°	62	62
55°	21	19
65°	14	14
75°	10	10
85°	7	6
90°	0	



TEST NUMBER: P366306

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8040-F6LBXVM1-WMH-BTR87

CANDELA DISTRIBUTION (FULL):

	0°
0°	4469.0
2.5°	4441.2
5°	4378.7
7.5°	4294.0
10°	4124.5
12.5°	3934.2
15°	3696.6
17.5°	3411.8
20°	3084.0
22.5°	2739.5
25°	2386.6
27.5°	1990.7
30°	1599.0
32.5°	1175.3
35°	698.8
37.5°	372.3
40°	209.8
42.5°	115.3
45°	62.5
47.5°	32.0
50°	26.4
52.5°	23.6
55°	20.8
57.5°	19.4
60°	18.1
62.5°	15.3
65°	13.9
67.5°	11.1
70°	11.1
72.5°	9.7
75°	9.7
77.5°	8.3
80°	8.3
82.5°	6.9
85°	6.9
87.5°	4.2
90°	0.0

(END OF REPORT)