

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364937

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364937
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3795.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364937

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P364937

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	425938
5°	416237
10°	383723
15°	339868
20°	287743
25°	227966
30°	160198
35°	66720
40°	22891
45°	6116
50°	3364
55°	3146
60°	2878
65°	2846
70°	2805
75°	3237
80°	4165
85°	6901



TEST NUMBER: P364937

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	536.7	14.1
10°-20°	1271.9	33.5
20°-30°	1305.8	34.4
30°-40°	552.9	14.6
40°-50°	68.0	1.8
50°-60°	22.5	0.6
60°-70°	16.6	0.4
70°-80°	12.8	0.3
80°-90°	7.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3114.4	82.1
0°-40°	3667.3	96.6
0°-60°	3757.8	99.0
0°-90°	3795.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3795.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5949	
5°	5791	537
15°	4585	1272
25°	2886	1306
35°	763	553
45°	60	68
55°	25	23
65°	17	17
75°	12	13
85°	8	8
90°	0	



TEST NUMBER: P364937

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR86

CANDELA DISTRIBUTION (FULL):

0°	
0°	5948.7
2.5°	5910.2
5°	5791.1
7.5°	5586.4
10°	5277.7
12.5°	4948.9
15°	4584.9
17.5°	4194.0
20°	3776.3
22.5°	3331.7
25°	2885.5
27.5°	2424.1
30°	1937.6
32.5°	1365.6
35°	763.3
37.5°	437.9
40°	244.9
42.5°	129.2
45°	60.4
47.5°	35.2
50°	30.2
52.5°	26.8
55°	25.2
57.5°	23.5
60°	20.1
62.5°	18.5
65°	16.8
67.5°	15.1
70°	13.4
72.5°	13.4
75°	11.7
77.5°	11.7
80°	10.1
82.5°	10.1
85°	8.4
87.5°	5.0
90°	0.0

(END OF REPORT)