

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364876

Luminaire Tested: **FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BL89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC, CLEAR 0.125", 4000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4053.1 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 40.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364876

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P364876

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	81	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	59	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156918
5°	153731
10°	141923
15°	126158
20°	107663
25°	90206
30°	70699
35°	37274
40°	17415
45°	6849
50°	1793
55°	486
60°	317
65°	284
70°	232
75°	306
80°	236
85°	470



TEST NUMBER: P364876

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	518.9	12.8
10°-20°	1238.9	30.6
20°-30°	1362.7	33.6
30°-40°	752.2	18.6
40°-50°	158.7	3.9
50°-60°	13.0	0.3
60°-70°	4.0	0.1
70°-80°	3.3	0.1
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3120.5	77.0
0°-40°	3872.7	95.6
0°-60°	4044.4	99.8
0°-90°	4053.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4053.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5745	
5°	5607	519
15°	4461	1239
25°	2993	1363
35°	1118	752
45°	177	159
55°	10	13
65°	4	4
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P364876

CATALOG NUMBER: FLD6BX40D010-FEU6B35-8050-F6LBXVM1-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5744.7
2.5°	5701.1
5°	5606.6
7.5°	5392.9
10°	5116.8
12.5°	4799.9
15°	4461.2
17.5°	4097.8
20°	3703.8
22.5°	3346.2
25°	2993.0
27.5°	2634.0
30°	2241.5
32.5°	1706.6
35°	1117.8
37.5°	742.8
40°	488.4
42.5°	308.2
45°	177.3
47.5°	93.0
50°	42.2
52.5°	17.4
55°	10.2
57.5°	7.3
60°	5.8
62.5°	4.4
65°	4.4
67.5°	2.9
70°	2.9
72.5°	4.4
75°	2.9
77.5°	2.9
80°	1.5
82.5°	1.5
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)