

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365662

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365662  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-MW  
Description: VANDAL RESISTANT OPEN, MATTE WHITE REFLECTOR, 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4485.0 lumens  
Efficiency: N/A  
Efficacy: 81.4 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.94  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365662

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-MW

### Luminous Intensity Polar Plot





TEST NUMBER: P365662

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 102 | 99  | 97  | 98  | 96  | 94  | 94  | 93  | 91  | 89  |
| 2   | 104 | 98  | 93  | 88  | 102 | 96  | 91  | 87  | 93  | 89  | 85  | 89  | 86  | 83  | 87  | 84  | 82  | 80  |
| 3   | 97  | 89  | 83  | 78  | 95  | 88  | 82  | 77  | 85  | 80  | 76  | 82  | 78  | 74  | 80  | 76  | 73  | 71  |
| 4   | 91  | 81  | 74  | 69  | 89  | 80  | 74  | 69  | 78  | 72  | 68  | 76  | 71  | 67  | 74  | 70  | 66  | 64  |
| 5   | 85  | 75  | 68  | 62  | 83  | 74  | 67  | 62  | 72  | 66  | 61  | 70  | 65  | 61  | 68  | 64  | 60  | 59  |
| 6   | 80  | 69  | 62  | 57  | 78  | 68  | 61  | 56  | 67  | 61  | 56  | 65  | 60  | 56  | 64  | 59  | 55  | 54  |
| 7   | 75  | 64  | 57  | 52  | 74  | 63  | 57  | 52  | 62  | 56  | 51  | 61  | 55  | 51  | 60  | 55  | 51  | 49  |
| 8   | 71  | 60  | 53  | 48  | 70  | 59  | 52  | 48  | 58  | 52  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 45  |
| 9   | 67  | 56  | 49  | 44  | 66  | 55  | 49  | 44  | 54  | 48  | 44  | 53  | 48  | 44  | 52  | 47  | 44  | 42  |
| 10  | 64  | 52  | 46  | 41  | 63  | 52  | 45  | 41  | 51  | 45  | 41  | 50  | 45  | 41  | 49  | 44  | 41  | 39  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 100572 |
| 5°  | 98403  |
| 10° | 93098  |
| 15° | 87331  |
| 20° | 81246  |
| 25° | 74579  |
| 30° | 63199  |
| 35° | 47471  |
| 40° | 34064  |
| 45° | 25480  |
| 50° | 20534  |
| 55° | 18220  |
| 60° | 16559  |
| 65° | 15176  |
| 70° | 13888  |
| 75° | 12717  |
| 80° | 11326  |
| 85° | 9340   |



TEST NUMBER: P365662

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 335.3  | 7.5       |
| 10°-20°   | 865.8  | 19.3      |
| 20°-30°   | 1121.3 | 25.0      |
| 30°-40°   | 897.6  | 20.0      |
| 40°-50°   | 523.4  | 11.7      |
| 50°-60°   | 345.0  | 7.7       |
| 60°-70°   | 234.1  | 5.2       |
| 70°-80°   | 128.1  | 2.9       |
| 80°-90°   | 34.5   | 0.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2322.4 | 51.8      |
| 0°-40°    | 3220.0 | 71.8      |
| 0°-60°    | 4088.4 | 91.2      |
| 0°-90°    | 4485.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4485.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3682 |      |
| 5°  | 3589 | 335  |
| 15° | 3088 | 866  |
| 25° | 2474 | 1121 |
| 35° | 1424 | 898  |
| 45° | 660  | 523  |
| 55° | 383  | 345  |
| 65° | 235  | 234  |
| 75° | 120  | 128  |
| 85° | 30   | 34   |
| 90° | 0    |      |



TEST NUMBER: P365662

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3681.9 |
| 2.5°  | 3658.3 |
| 5°    | 3588.8 |
| 7.5°  | 3489.4 |
| 10°   | 3356.5 |
| 12.5° | 3232.3 |
| 15°   | 3088.2 |
| 17.5° | 2937.9 |
| 20°   | 2795.0 |
| 22.5° | 2645.9 |
| 25°   | 2474.5 |
| 27.5° | 2262.1 |
| 30°   | 2003.7 |
| 32.5° | 1724.2 |
| 35°   | 1423.6 |
| 37.5° | 1171.4 |
| 40°   | 955.3  |
| 42.5° | 791.3  |
| 45°   | 659.6  |
| 47.5° | 559.0  |
| 50°   | 483.2  |
| 52.5° | 426.1  |
| 55°   | 382.6  |
| 57.5° | 342.9  |
| 60°   | 303.1  |
| 62.5° | 268.3  |
| 65°   | 234.8  |
| 67.5° | 205.0  |
| 70°   | 173.9  |
| 72.5° | 146.6  |
| 75°   | 120.5  |
| 77.5° | 95.7   |
| 80°   | 72.0   |
| 82.5° | 49.7   |
| 85°   | 29.8   |
| 87.5° | 11.2   |
| 90°   | 0.0    |

(END OF REPORT)