

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P236151

Luminaire Tested: **FLD6BX50D010 EU6B3/58040 F6LBXVM1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P236151
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010 EU6B3/58040 F6LBXVM1LI
Description: FAILSAFE 6 INCH RECESSED LED DOWNLIGHT
6" LED Vandal Resistant, Medium (50° Beam), Specular Clear, Bottom open
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4954.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P236151

CATALOG NUMBER: FLD6BX50D010 EU6B3/58040 F6LBXVM1LI

Luminous Intensity Polar Plot





TEST NUMBER: P236151

CATALOG NUMBER: FLD6BX50D010 EU6B3/58040 F6LBXVM1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	336792
5°	332184
10°	316807
15°	295969
20°	276447
25°	250623
30°	204997
35°	140237
40°	83496
45°	45228
50°	22339
55°	13661
60°	9134
65°	6175
70°	3815
75°	2521
80°	3757
85°	0



TEST NUMBER: P236151

CATALOG NUMBER: FLD6BX50D010 EU6B3/58040 F6LBXVM1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	474.2	9.6
10°-20°	1230.6	24.8
20°-30°	1567.9	31.6
30°-40°	1108.1	22.4
40°-50°	404.5	8.2
50°-60°	112.1	2.3
60°-70°	40.7	0.8
70°-80°	14.5	0.3
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3272.7	66.1
0°-40°	4380.8	88.4
0°-60°	4897.5	98.9
0°-90°	4954.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4954.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5162	
5°	5072	474
15°	4382	1231
25°	3482	1568
35°	1761	1108
45°	490	405
55°	120	112
65°	40	41
75°	10	14
85°	0	1
90°	0	



TEST NUMBER: P236151

CATALOG NUMBER: FLD6BX50D010 EU6B3/58040 F6LBXVM1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5162.3
2.5°	5142.3
5°	5072.3
7.5°	4932.2
10°	4782.2
12.5°	4582.1
15°	4382.0
17.5°	4181.9
20°	3981.8
22.5°	3741.7
25°	3481.6
27.5°	3121.4
30°	2721.2
32.5°	2241.0
35°	1760.8
37.5°	1340.6
40°	980.4
42.5°	710.3
45°	490.2
47.5°	330.1
50°	220.1
52.5°	150.1
55°	120.1
57.5°	90.0
60°	70.0
62.5°	50.0
65°	40.0
67.5°	30.0
70°	20.0
72.5°	20.0
75°	10.0
77.5°	10.0
80°	10.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)