

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364901

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR86**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364901  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR86  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3558.9 lumens  
Efficiency: N/A  
Efficacy: 64.6 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364901

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR86

### Luminous Intensity Polar Plot





TEST NUMBER: P364901

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR86

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	399452
5°	390348
10°	359860
15°	318727
20°	269844
25°	213785
30°	150235
35°	62568
40°	21470
45°	5731
50°	3152
55°	2946
60°	2707
65°	2660
70°	2638
75°	3043
80°	3876
85°	6490



TEST NUMBER: P364901

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR86

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	503.3	14.1
10°-20°	1192.8	33.5
20°-30°	1224.6	34.4
30°-40°	518.5	14.6
40°-50°	63.7	1.8
50°-60°	21.1	0.6
60°-70°	15.6	0.4
70°-80°	12.0	0.3
80°-90°	7.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2920.7	82.1
0°-40°	3439.2	96.6
0°-60°	3524.0	99.0
0°-90°	3558.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3558.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5579	
5°	5431	503
15°	4300	1193
25°	2706	1225
35°	716	519
45°	57	64
55°	24	21
65°	16	16
75°	11	12
85°	8	7
90°	0	



TEST NUMBER: P364901

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8027-F6LBXVM1-LI-BTR86

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5578.8
2.5°	5542.6
5°	5430.9
7.5°	5239.0
10°	4949.5
12.5°	4641.1
15°	4299.7
17.5°	3933.2
20°	3541.4
22.5°	3124.5
25°	2706.0
27.5°	2273.4
30°	1817.1
32.5°	1280.6
35°	715.8
37.5°	410.6
40°	229.7
42.5°	121.1
45°	56.6
47.5°	33.0
50°	28.3
52.5°	25.2
55°	23.6
57.5°	22.0
60°	18.9
62.5°	17.3
65°	15.7
67.5°	14.2
70°	12.6
72.5°	12.6
75°	11.0
77.5°	11.0
80°	9.4
82.5°	9.4
85°	7.9
87.5°	4.7
90°	0.0

(END OF REPORT)