

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364943

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BL84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364943  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BL84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,  
BOTTOM LENS POLYCARBONATE, CLEAR 0.125", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4677.0 lumens  
Efficiency: N/A  
Efficacy: 84.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364943

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BL84

### Luminous Intensity Polar Plot





TEST NUMBER: P364943

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BL84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	179942
5°	176522
10°	163014
15°	145263
20°	124058
25°	104188
30°	81789
35°	42382
40°	20239
45°	7965
50°	2099
55°	586
60°	388
65°	343
70°	280
75°	369
80°	283
85°	564



TEST NUMBER: P364943

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BL84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	597.0	12.8
10°-20°	1427.6	30.5
20°-30°	1576.3	33.7
30°-40°	867.3	18.5
40°-50°	183.3	3.9
50°-60°	15.5	0.3
60°-70°	4.8	0.1
70°-80°	3.5	0.1
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3600.9	77.0
0°-40°	4468.2	95.5
0°-60°	4667.0	99.8
0°-90°	4677.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4677.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6588	
5°	6438	597
15°	5137	1428
25°	3457	1576
35°	1271	867
45°	206	183
55°	12	16
65°	5	5
75°	4	3
85°	2	2
90°	0	



TEST NUMBER: P364943

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BL84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6587.6
2.5°	6584.1
5°	6437.8
7.5°	6212.2
10°	5877.2
12.5°	5544.1
15°	5136.8
17.5°	4722.6
20°	4267.8
22.5°	3869.4
25°	3456.9
27.5°	3058.5
30°	2593.1
32.5°	1979.6
35°	1271.0
37.5°	856.7
40°	567.6
42.5°	354.3
45°	206.2
47.5°	105.8
50°	49.4
52.5°	21.2
55°	12.3
57.5°	8.8
60°	7.1
62.5°	5.3
65°	5.3
67.5°	3.5
70°	3.5
72.5°	5.3
75°	3.5
77.5°	1.8
80°	1.8
82.5°	1.8
85°	1.8
87.5°	1.8
90°	0.0

(END OF REPORT)