

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364975

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR89BI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364975  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR89BI  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3959.0 lumens  
Efficiency: N/A  
Efficacy: 71.9 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364975

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR89BI

### Luminous Intensity Polar Plot





TEST NUMBER: P364975

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR89BI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	443609
5°	433308
10°	398257
15°	354442
20°	300217
25°	238734
30°	167846
35°	70050
40°	24190
45°	6258
50°	3164
55°	2921
60°	2864
65°	2829
70°	2805
75°	3707
80°	4123
85°	6819



TEST NUMBER: P364975

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR89BI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	558.1	14.1
10°-20°	1324.5	33.5
20°-30°	1366.7	34.5
30°-40°	581.3	14.7
40°-50°	69.8	1.8
50°-60°	21.1	0.5
60°-70°	16.5	0.4
70°-80°	13.3	0.3
80°-90°	7.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3249.3	82.1
0°-40°	3830.7	96.8
0°-60°	3921.5	99.1
0°-90°	3959.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3959.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6196	
5°	6029	558
15°	4782	1325
25°	3022	1367
35°	801	581
45°	62	70
55°	23	21
65°	17	17
75°	13	13
85°	8	8
90°	0	



TEST NUMBER: P364975

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BTR89BI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6195.5
2.5°	6155.5
5°	6028.6
7.5°	5808.2
10°	5477.6
12.5°	5152.1
15°	4781.5
17.5°	4364.1
20°	3940.0
22.5°	3497.6
25°	3021.8
27.5°	2531.0
30°	2030.1
32.5°	1439.1
35°	801.4
37.5°	460.8
40°	258.8
42.5°	133.6
45°	61.8
47.5°	33.4
50°	28.4
52.5°	25.0
55°	23.4
57.5°	21.7
60°	20.0
62.5°	18.4
65°	16.7
67.5°	15.0
70°	13.4
72.5°	13.4
75°	13.4
77.5°	11.7
80°	10.0
82.5°	10.0
85°	8.3
87.5°	5.0
90°	0.0

(END OF REPORT)