

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365692

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365692  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR85  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3185.0 lumens  
Efficiency: N/A  
Efficacy: 57.8 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.84  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365692

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR85

### Luminous Intensity Polar Plot





TEST NUMBER: P365692

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	72	65	60	80	71	64	60	69	63	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	60	55	65	59	55	64	58	54	62	58	54	52
8	73	63	56	51	72	62	55	51	61	55	51	60	54	51	59	54	50	49
9	70	59	52	48	68	58	52	48	57	51	47	56	51	47	55	51	47	45
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	221307
5°	217222
10°	206348
15°	193251
20°	175947
25°	146773
30°	106424
35°	73223
40°	53829
45°	43694
50°	38007
55°	33580
60°	29214
65°	24770
70°	20035
75°	14496
80°	9690
85°	10351



TEST NUMBER: P365692

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR85

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	282.6	8.9
10°-20°	728.1	22.9
20°-30°	835.6	26.2
30°-40°	540.8	17.0
40°-50°	339.8	10.7
50°-60°	241.8	7.6
60°-70°	145.8	4.6
70°-80°	58.0	1.8
80°-90°	12.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1846.3	58.0
0°-40°	2387.1	75.0
0°-60°	2968.7	93.2
0°-90°	3185.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3185.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3091	
5°	3022	283
15°	2607	728
25°	1858	836
35°	838	541
45°	432	340
55°	269	242
65°	146	146
75°	52	58
85°	13	13
90°	0	



TEST NUMBER: P365692

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR85

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3090.8
2.5°	3076.4
5°	3022.2
7.5°	2941.0
10°	2838.1
12.5°	2724.3
15°	2607.0
17.5°	2475.2
20°	2309.1
22.5°	2108.7
25°	1857.8
27.5°	1577.9
30°	1287.2
32.5°	1041.7
35°	837.7
37.5°	687.9
40°	575.9
42.5°	494.7
45°	431.5
47.5°	382.7
50°	341.2
52.5°	305.1
55°	269.0
57.5°	236.5
60°	204.0
62.5°	175.1
65°	146.2
67.5°	119.2
70°	95.7
72.5°	72.2
75°	52.4
77.5°	36.1
80°	23.5
82.5°	14.4
85°	12.6
87.5°	7.2
90°	0.0

(END OF REPORT)