

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365693

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-17)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3086.0 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365693

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P365693

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	98	93	89	94	91	87		91	88	85		88	86	84	82
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	72	69	68
5	87	78	71	66	86	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	66	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	51	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		53	48	45		53	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	218285
5°	214318
10°	203534
15°	190241
20°	172160
25°	142973
30°	102588
35°	70409
40°	51829
45°	41881
50°	36414
55°	32020
60°	27667
65°	23567
70°	18527
75°	13002
80°	8206
85°	8873



TEST NUMBER: P365693

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.9	9.0
10°-20°	716.1	23.2
20°-30°	812.3	26.3
30°-40°	520.6	16.9
40°-50°	326.3	10.6
50°-60°	230.2	7.5
60°-70°	138.3	4.5
70°-80°	52.8	1.7
80°-90°	10.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1807.3	58.6
0°-40°	2327.9	75.4
0°-60°	2884.4	93.5
0°-90°	3086.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3086.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3049	
5°	2982	279
15°	2566	716
25°	1810	812
35°	806	521
45°	414	326
55°	256	230
65°	139	138
75°	47	53
85°	11	11
90°	0	



TEST NUMBER: P365693

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-MW-BTR86

CANDELA DISTRIBUTION (FULL):

0°	
0°	3048.6
2.5°	3039.6
5°	2981.8
7.5°	2904.1
10°	2799.4
12.5°	2685.6
15°	2566.4
17.5°	2430.9
20°	2259.4
22.5°	2058.9
25°	1809.7
27.5°	1522.5
30°	1240.8
32.5°	1002.4
35°	805.5
37.5°	662.8
40°	554.5
42.5°	475.0
45°	413.6
47.5°	368.4
50°	326.9
52.5°	290.8
55°	256.5
57.5°	224.0
60°	193.2
62.5°	166.2
65°	139.1
67.5°	113.8
70°	88.5
72.5°	66.8
75°	47.0
77.5°	32.5
80°	19.9
82.5°	12.6
85°	10.8
87.5°	5.4
90°	0.0

(END OF REPORT)