

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366411

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR84**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P366411  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR84  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4020.9 lumens  
Efficiency: N/A  
Efficacy: 73.0 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P366411

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR84

### Luminous Intensity Polar Plot





TEST NUMBER: P366411

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR84

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	415728
5°	408885
10°	389597
15°	356006
20°	305299
25°	244967
30°	171757
35°	79351
40°	25470
45°	8222
50°	3821
55°	3383
60°	3365
65°	3050
70°	3015
75°	3486
80°	4453
85°	7394



TEST NUMBER: P366411

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR84

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	533.5	13.3
10°-20°	1329.0	33.1
20°-30°	1395.7	34.7
30°-40°	619.3	15.4
40°-50°	80.0	2.0
50°-60°	25.0	0.6
60°-70°	17.6	0.4
70°-80°	12.8	0.3
80°-90°	7.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3258.2	81.0
0°-40°	3877.6	96.4
0°-60°	3982.6	99.0
0°-90°	4020.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4020.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5806	
5°	5689	534
15°	4803	1329
25°	3101	1396
35°	908	619
45°	81	80
55°	27	25
65°	18	18
75°	13	13
85°	9	8
90°	0	



TEST NUMBER: P366411

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR84

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5806.1
2.5°	5770.0
5°	5688.8
7.5°	5578.7
10°	5358.5
12.5°	5111.3
15°	4802.6
17.5°	4432.6
20°	4006.7
22.5°	3559.1
25°	3100.7
27.5°	2586.3
30°	2077.4
32.5°	1526.9
35°	907.8
37.5°	483.7
40°	272.5
42.5°	149.8
45°	81.2
47.5°	41.5
50°	34.3
52.5°	30.7
55°	27.1
57.5°	25.3
60°	23.5
62.5°	19.9
65°	18.0
67.5°	14.4
70°	14.4
72.5°	12.6
75°	12.6
77.5°	10.8
80°	10.8
82.5°	9.0
85°	9.0
87.5°	5.4
90°	0.0

(END OF REPORT)