

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364936

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364936  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR85  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3917.0 lumens  
Efficiency: N/A  
Efficacy: 71.1 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364936

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR85

### Luminous Intensity Polar Plot





TEST NUMBER: P364936

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	439635
5°	429613
10°	396061
15°	350794
20°	296993
25°	235289
30°	165349
35°	68861
40°	23629
45°	6309
50°	3475
55°	3246
60°	2979
65°	2931
70°	2910
75°	3347
80°	4288
85°	7147



TEST NUMBER: P364936

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR85

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	553.9	14.1
10°-20°	1312.8	33.5
20°-30°	1347.7	34.4
30°-40°	570.7	14.6
40°-50°	70.2	1.8
50°-60°	23.2	0.6
60°-70°	17.1	0.4
70°-80°	13.3	0.3
80°-90°	8.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3214.5	82.1
0°-40°	3785.2	96.6
0°-60°	3878.6	99.0
0°-90°	3917.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3917.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6140	
5°	5977	554
15°	4732	1313
25°	2978	1348
35°	788	571
45°	62	70
55°	26	23
65°	17	17
75°	12	13
85°	9	8
90°	0	



TEST NUMBER: P364936

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR85

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6140.0
2.5°	6100.2
5°	5977.2
7.5°	5766.0
10°	5447.4
12.5°	5108.0
15°	4732.3
17.5°	4328.8
20°	3897.7
22.5°	3438.8
25°	2978.2
27.5°	2502.1
30°	1999.9
32.5°	1409.5
35°	787.8
37.5°	451.9
40°	252.8
42.5°	133.3
45°	62.3
47.5°	36.4
50°	31.2
52.5°	27.7
55°	26.0
57.5°	24.2
60°	20.8
62.5°	19.0
65°	17.3
67.5°	15.6
70°	13.9
72.5°	13.9
75°	12.1
77.5°	12.1
80°	10.4
82.5°	10.4
85°	8.7
87.5°	5.2
90°	0.0

(END OF REPORT)