

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366415

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3881.9 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366415

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P366415

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	402109
5°	396687
10°	377594
15°	343263
20°	295584
25°	236285
30°	165680
35°	77069
40°	24349
45°	7605
50°	3353
55°	3121
60°	2864
65°	2541
70°	2805
75°	3237
80°	4123
85°	6819



TEST NUMBER: P366415

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	516.6	13.3
10°-20°	1284.0	33.1
20°-30°	1349.9	34.8
30°-40°	598.9	15.4
40°-50°	74.9	1.9
50°-60°	22.4	0.6
60°-70°	15.7	0.4
70°-80°	12.4	0.3
80°-90°	7.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3150.5	81.2
0°-40°	3749.3	96.6
0°-60°	3846.6	99.1
0°-90°	3881.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3881.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5616	
5°	5519	517
15°	4631	1284
25°	2991	1350
35°	882	599
45°	75	75
55°	25	22
65°	15	16
75°	12	12
85°	8	7
90°	0	



TEST NUMBER: P366415

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-WMH-BTR89BI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5615.9
2.5°	5579.2
5°	5519.1
7.5°	5395.5
10°	5193.4
12.5°	4946.3
15°	4630.7
17.5°	4275.0
20°	3879.2
22.5°	3450.0
25°	2990.8
27.5°	2503.2
30°	2003.9
32.5°	1474.5
35°	881.7
37.5°	469.2
40°	260.5
42.5°	141.9
45°	75.1
47.5°	36.7
50°	30.1
52.5°	26.7
55°	25.0
57.5°	23.4
60°	20.0
62.5°	18.4
65°	15.0
67.5°	13.4
70°	13.4
72.5°	11.7
75°	11.7
77.5°	11.7
80°	10.0
82.5°	8.3
85°	8.3
87.5°	5.0
90°	0.0

(END OF REPORT)