

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P236168

Luminaire Tested: **FLD6BX60D010 EU6B6/78040 F6LBXVM1LIBL85**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P236168  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX60D010 EU6B6/78040 F6LBXVM1LIBL85  
Description: FAILSAFE 6 INCH RECESSED LED DOWNLIGHT  
6" LED Vandal Resistant, Medium (50° Beam), Specular Clear, Bottom lens,  
0.187" clear polycarbonate  
Light Source: (1) 4000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4704.7 lumens  
Efficiency: N/A  
Efficacy: 75.3 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 62.48  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P236168

CATALOG NUMBER: FLD6BX60D010 EU6B6/78040 F6LBXVM1LIBL85

### Luminous Intensity Polar Plot





TEST NUMBER: P236168

CATALOG NUMBER: FLD6BX60D010 EU6B6/78040 F6LBXVM1LIBL85

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 95  | 93  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 97  | 93  | 97  | 94  | 91  | 94  | 92  | 89  | 91  | 89  | 87  | 86  |
| 3   | 102 | 95  | 90  | 85  | 100 | 93  | 89  | 85  | 91  | 87  | 83  | 88  | 85  | 82  | 86  | 83  | 81  | 79  |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 82  | 77  | 85  | 80  | 77  | 83  | 79  | 76  | 81  | 78  | 75  | 73  |
| 5   | 91  | 82  | 76  | 72  | 89  | 81  | 76  | 71  | 79  | 74  | 71  | 78  | 73  | 70  | 76  | 72  | 69  | 68  |
| 6   | 86  | 77  | 71  | 66  | 85  | 76  | 70  | 66  | 74  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 64  | 63  |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 65  | 61  | 69  | 64  | 60  | 68  | 63  | 60  | 59  |
| 8   | 77  | 68  | 61  | 57  | 76  | 67  | 61  | 57  | 66  | 60  | 57  | 65  | 60  | 56  | 64  | 59  | 56  | 55  |
| 9   | 74  | 64  | 57  | 53  | 72  | 63  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 51  |
| 10  | 70  | 60  | 54  | 50  | 69  | 59  | 54  | 50  | 59  | 53  | 50  | 58  | 53  | 49  | 57  | 53  | 49  | 48  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 319849 |
| 5°  | 315471 |
| 10° | 300868 |
| 15° | 281076 |
| 20° | 262541 |
| 25° | 238011 |
| 30° | 194684 |
| 35° | 133181 |
| 40° | 79298  |
| 45° | 42958  |
| 50° | 21213  |
| 55° | 12967  |
| 60° | 8677   |
| 65° | 5866   |
| 70° | 3624   |
| 75° | 2395   |
| 80° | 3569   |
| 85° | 0      |



TEST NUMBER: P236168

CATALOG NUMBER: FLD6BX60D010 EU6B6/78040 F6LBXVM1LIBL85

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 450.4  | 9.6       |
| 10°-20°   | 1168.7 | 24.8      |
| 20°-30°   | 1489.0 | 31.6      |
| 30°-40°   | 1052.3 | 22.4      |
| 40°-50°   | 384.2  | 8.2       |
| 50°-60°   | 106.5  | 2.3       |
| 60°-70°   | 38.6   | 0.8       |
| 70°-80°   | 13.8   | 0.3       |
| 80°-90°   | 1.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 3108.1 | 66.1      |
| 0°-40°    | 4160.4 | 88.4      |
| 0°-60°    | 4651.1 | 98.9      |
| 0°-90°    | 4704.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4704.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4903 |      |
| 5°  | 4817 | 450  |
| 15° | 4162 | 1169 |
| 25° | 3306 | 1489 |
| 35° | 1672 | 1052 |
| 45° | 466  | 384  |
| 55° | 114  | 106  |
| 65° | 38   | 39   |
| 75° | 10   | 14   |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P236168

CATALOG NUMBER: FLD6BX60D010 EU6B6/78040 F6LBXVM1LIBL85

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 4902.6 |
| 2.5°  | 4883.6 |
| 5°    | 4817.1 |
| 7.5°  | 4684.1 |
| 10°   | 4541.6 |
| 12.5° | 4351.5 |
| 15°   | 4161.5 |
| 17.5° | 3971.5 |
| 20°   | 3781.5 |
| 22.5° | 3553.4 |
| 25°   | 3306.4 |
| 27.5° | 2964.4 |
| 30°   | 2584.3 |
| 32.5° | 2128.3 |
| 35°   | 1672.2 |
| 37.5° | 1273.2 |
| 40°   | 931.1  |
| 42.5° | 674.6  |
| 45°   | 465.6  |
| 47.5° | 313.5  |
| 50°   | 209.0  |
| 52.5° | 142.5  |
| 55°   | 114.0  |
| 57.5° | 85.5   |
| 60°   | 66.5   |
| 62.5° | 47.5   |
| 65°   | 38.0   |
| 67.5° | 28.5   |
| 70°   | 19.0   |
| 72.5° | 19.0   |
| 75°   | 9.5    |
| 77.5° | 9.5    |
| 80°   | 9.5    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)