

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364938

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3864.0 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364938

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P364938

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	433685
5°	423799
10°	390703
15°	346043
20°	292970
25°	232106
30°	163109
35°	67935
40°	23311
45°	6228
50°	3420
55°	3196
60°	2936
65°	2897
70°	2868
75°	3320
80°	4206
85°	6983



TEST NUMBER: P364938

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	546.4	14.1
10°-20°	1295.1	33.5
20°-30°	1329.5	34.4
30°-40°	563.0	14.6
40°-50°	69.2	1.8
50°-60°	22.9	0.6
60°-70°	16.9	0.4
70°-80°	13.1	0.3
80°-90°	7.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3171.0	82.1
0°-40°	3734.0	96.6
0°-60°	3826.1	99.0
0°-90°	3864.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3864.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6057	
5°	5896	546
15°	4668	1295
25°	2938	1329
35°	777	563
45°	62	69
55°	26	23
65°	17	17
75°	12	13
85°	8	8
90°	0	



TEST NUMBER: P364938

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-LI-BTR87

CANDELA DISTRIBUTION (FULL):

0°	
0°	6056.9
2.5°	6017.6
5°	5896.3
7.5°	5688.0
10°	5373.7
12.5°	5038.9
15°	4668.2
17.5°	4270.2
20°	3844.9
22.5°	3392.3
25°	2937.9
27.5°	2468.2
30°	1972.8
32.5°	1390.4
35°	777.2
37.5°	445.8
40°	249.4
42.5°	131.5
45°	61.5
47.5°	35.9
50°	30.7
52.5°	27.3
55°	25.6
57.5°	23.9
60°	20.5
62.5°	18.8
65°	17.1
67.5°	15.4
70°	13.7
72.5°	13.7
75°	12.0
77.5°	12.0
80°	10.2
82.5°	10.2
85°	8.5
87.5°	5.1
90°	0.0

(END OF REPORT)