

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364991

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4157.0 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364991

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P364991

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	466572
5°	455941
10°	420323
15°	372284
20°	315189
25°	249708
30°	175477
35°	73083
40°	25078
45°	6703
50°	3687
55°	3445
60°	3165
65°	3117
70°	3077
75°	3569
80°	4536
85°	7558



TEST NUMBER: P364991

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	587.9	14.1
10°-20°	1393.3	33.5
20°-30°	1430.3	34.4
30°-40°	605.7	14.6
40°-50°	74.5	1.8
50°-60°	24.7	0.6
60°-70°	18.2	0.4
70°-80°	14.1	0.3
80°-90°	8.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3411.4	82.1
0°-40°	4017.1	96.6
0°-60°	4116.2	99.0
0°-90°	4157.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4157.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6516	
5°	6344	588
15°	5022	1393
25°	3161	1430
35°	836	606
45°	66	74
55°	28	25
65°	18	18
75°	13	14
85°	9	8
90°	0	



TEST NUMBER: P364991

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-LI-BTR86

CANDELA DISTRIBUTION (FULL):

	0°
0°	6516.2
2.5°	6473.9
5°	6343.5
7.5°	6119.3
10°	5781.1
12.5°	5421.0
15°	5022.2
17.5°	4594.0
20°	4136.5
22.5°	3649.5
25°	3160.7
27.5°	2655.4
30°	2122.4
32.5°	1495.8
35°	836.1
37.5°	479.6
40°	268.3
42.5°	141.5
45°	66.2
47.5°	38.6
50°	33.1
52.5°	29.4
55°	27.6
57.5°	25.7
60°	22.1
62.5°	20.2
65°	18.4
67.5°	16.5
70°	14.7
72.5°	14.7
75°	12.9
77.5°	12.9
80°	11.0
82.5°	11.0
85°	9.2
87.5°	5.5
90°	0.0

(END OF REPORT)