

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365705

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL89BW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-35)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL89BW
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS ACRYLIC OPAL SMOOTH, CLEAR 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3445.0 lumens
Efficiency: N/A
Efficacy: 59.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365705

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL89BW

Luminous Intensity Polar Plot





TEST NUMBER: P365705

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL89BW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	69	63		72	67	62		70	65	61	59
4	83	71	62	55	80	69	61	55	67	60	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	47		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	43	36	63	51	42	36	49	41	36		48	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		44	37	32		42	36	32	30
9	56	43	35	29	55	42	35	29	41	34	29		40	34	29		39	33	29	27
10	53	40	32	26	52	39	32	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33538
5°	33562
10°	33367
15°	33211
20°	32862
25°	32689
30°	32342
35°	31965
40°	31593
45°	31201
50°	30673
55°	30102
60°	29107
65°	28019
70°	26227
75°	23377
80°	18923
85°	11377



TEST NUMBER: P365705

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL89BW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.1	3.4
10°-20°	331.2	9.6
20°-30°	499.0	14.5
30°-40°	600.0	17.4
40°-50°	622.7	18.1
50°-60°	564.4	16.4
60°-70°	428.3	12.4
70°-80°	234.3	6.8
80°-90°	49.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	946.3	27.5
0°-40°	1546.3	44.9
0°-60°	2733.4	79.3
0°-90°	3445.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3445.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1228	
5°	1224	116
15°	1174	331
25°	1085	499
35°	959	600
45°	808	623
55°	632	564
65°	434	428
75°	222	234
85°	36	49
90°	0	



TEST NUMBER: P365705

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-MW-BL89BW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1227.8
2.5°	1225.9
5°	1224.0
7.5°	1214.5
10°	1203.0
12.5°	1191.6
15°	1174.4
17.5°	1155.3
20°	1130.5
22.5°	1105.6
25°	1084.6
27.5°	1056.0
30°	1025.4
32.5°	993.0
35°	958.6
37.5°	924.2
40°	886.0
42.5°	847.8
45°	807.7
47.5°	765.7
50°	721.8
52.5°	677.9
55°	632.1
57.5°	586.2
60°	532.8
62.5°	485.0
65°	433.5
67.5°	381.9
70°	328.4
72.5°	275.0
75°	221.5
77.5°	168.0
80°	120.3
82.5°	74.5
85°	36.3
87.5°	9.5
90°	0.0

(END OF REPORT)