

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366375

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR84**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR84
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.125", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3885.0 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366375

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR84

Luminous Intensity Polar Plot





TEST NUMBER: P366375

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR84

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	401665
5°	395056
10°	376423
15°	343967
20°	294974
25°	236680
30°	165944
35°	76667
40°	24611
45°	7949
50°	3687
55°	3271
60°	3251
65°	2948
70°	2931
75°	3375
80°	4330
85°	7147



TEST NUMBER: P366375

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR84

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.5	13.3
10°-20°	1284.0	33.1
20°-30°	1348.5	34.7
30°-40°	598.4	15.4
40°-50°	77.3	2.0
50°-60°	24.2	0.6
60°-70°	17.1	0.4
70°-80°	12.5	0.3
80°-90°	7.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3148.0	81.0
0°-40°	3746.4	96.4
0°-60°	3847.9	99.0
0°-90°	3885.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3885.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5610	
5°	5496	515
15°	4640	1284
25°	2996	1349
35°	877	598
45°	78	77
55°	26	24
65°	17	17
75°	12	12
85°	9	8
90°	0	



TEST NUMBER: P366375

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR84

CANDELA DISTRIBUTION (FULL):

0°	
0°	5609.7
2.5°	5574.9
5°	5496.4
7.5°	5390.0
10°	5177.3
12.5°	4938.4
15°	4640.2
17.5°	4282.7
20°	3871.2
22.5°	3438.7
25°	2995.8
27.5°	2498.8
30°	2007.1
32.5°	1475.2
35°	877.1
37.5°	467.3
40°	263.3
42.5°	144.7
45°	78.5
47.5°	40.1
50°	33.1
52.5°	29.6
55°	26.2
57.5°	24.4
60°	22.7
62.5°	19.2
65°	17.4
67.5°	14.0
70°	14.0
72.5°	12.2
75°	12.2
77.5°	10.5
80°	10.5
82.5°	8.7
85°	8.7
87.5°	5.2
90°	0.0

(END OF REPORT)