

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366378

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR87**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR87
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.375", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3804.0 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366378

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR87

Luminous Intensity Polar Plot





TEST NUMBER: P366378

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR87

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	393295
5°	386819
10°	368571
15°	336792
20°	288825
25°	231750
30°	162480
35°	75067
40°	24096
45°	7777
50°	3609
55°	3196
60°	3179
65°	2897
70°	2868
75°	3320
80°	4206
85°	6983



TEST NUMBER: P366378

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR87

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	504.7	13.3
10°-20°	1257.3	33.1
20°-30°	1320.4	34.7
30°-40°	585.9	15.4
40°-50°	75.7	2.0
50°-60°	23.6	0.6
60°-70°	16.7	0.4
70°-80°	12.2	0.3
80°-90°	7.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3082.4	81.0
0°-40°	3668.3	96.4
0°-60°	3767.7	99.0
0°-90°	3804.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3804.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5493	
5°	5382	505
15°	4543	1257
25°	2933	1320
35°	859	586
45°	77	76
55°	26	24
65°	17	17
75°	12	12
85°	8	7
90°	0	



TEST NUMBER: P366378

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8035-F6LBXVM1-WMH-BTR87

CANDELA DISTRIBUTION (FULL):

0°	
0°	5492.8
2.5°	5458.6
5°	5381.8
7.5°	5277.6
10°	5069.3
12.5°	4835.4
15°	4543.4
17.5°	4193.4
20°	3790.5
22.5°	3367.0
25°	2933.4
27.5°	2446.7
30°	1965.2
32.5°	1444.5
35°	858.8
37.5°	457.6
40°	257.8
42.5°	141.7
45°	76.8
47.5°	39.3
50°	32.4
52.5°	29.0
55°	25.6
57.5°	23.9
60°	22.2
62.5°	18.8
65°	17.1
67.5°	13.7
70°	13.7
72.5°	12.0
75°	12.0
77.5°	10.2
80°	10.2
82.5°	8.5
85°	8.5
87.5°	5.1
90°	0.0

(END OF REPORT)