

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364957

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BTR89BI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BTR89BI
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR RFI 0.125", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3865.0 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364957

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BTR89BI

Luminous Intensity Polar Plot





TEST NUMBER: P364957

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BTR89BI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	433077
5°	423015
10°	388805
15°	346021
20°	293092
25°	233069
30°	163861
35°	68381
40°	23610
45°	6106
50°	3086
55°	2846
60°	2807
65°	2762
70°	2722
75°	3596
80°	4041
85°	6654



TEST NUMBER: P364957

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BTR89BI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	544.9	14.1
10°-20°	1293.1	33.5
20°-30°	1334.3	34.5
30°-40°	567.5	14.7
40°-50°	68.1	1.8
50°-60°	20.6	0.5
60°-70°	16.1	0.4
70°-80°	12.9	0.3
80°-90°	7.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3172.2	82.1
0°-40°	3739.7	96.8
0°-60°	3828.4	99.1
0°-90°	3865.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3865.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6048	
5°	5885	545
15°	4668	1293
25°	2950	1334
35°	782	568
45°	60	68
55°	23	21
65°	16	16
75°	13	13
85°	8	8
90°	0	



TEST NUMBER: P364957

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI-BTR89BI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6048.4
2.5°	6009.3
5°	5885.4
7.5°	5670.3
10°	5347.6
12.5°	5029.8
15°	4667.9
17.5°	4260.5
20°	3846.5
22.5°	3414.6
25°	2950.1
27.5°	2470.9
30°	1981.9
32.5°	1404.9
35°	782.3
37.5°	449.8
40°	252.6
42.5°	130.4
45°	60.3
47.5°	32.6
50°	27.7
52.5°	24.4
55°	22.8
57.5°	21.2
60°	19.6
62.5°	17.9
65°	16.3
67.5°	14.7
70°	13.0
72.5°	13.0
75°	13.0
77.5°	11.4
80°	9.8
82.5°	9.8
85°	8.1
87.5°	4.9
90°	0.0

(END OF REPORT)