

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P366430

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-WMH-BTR85**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P366430
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-30)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-WMH-BTR85
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, WARM HAZE REFLECTOR,
BOTTOM TRIM POLYCARBONATE, CLEAR 0.187", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4225.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.8
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P366430

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-WMH-BTR85

Luminous Intensity Polar Plot





TEST NUMBER: P366430

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-WMH-BTR85

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	80	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	74	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	73	70	67	66
8	82	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	64	61	78	69	64	61	69	64	60	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	436821
5°	429628
10°	409366
15°	374071
20°	320790
25°	257395
30°	180463
35°	83380
40°	26770
45°	8638
50°	4010
55°	3545
60°	3537
65°	3219
70°	3182
75°	3679
80°	4701
85°	7805



TEST NUMBER: P366430

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-WMH-BTR85

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	560.6	13.3
10°-20°	1396.4	33.1
20°-30°	1466.5	34.7
30°-40°	650.8	15.4
40°-50°	84.1	2.0
50°-60°	26.2	0.6
60°-70°	18.6	0.4
70°-80°	13.6	0.3
80°-90°	8.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3423.6	81.0
0°-40°	4074.3	96.4
0°-60°	4184.6	99.0
0°-90°	4225.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4225.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6101	
5°	5977	561
15°	5046	1396
25°	3258	1467
35°	954	651
45°	85	84
55°	28	26
65°	19	19
75°	13	14
85°	10	8
90°	0	



TEST NUMBER: P366430

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8027-F6LBXVM1-WMH-BTR85

CANDELA DISTRIBUTION (FULL):

0°	
0°	6100.7
2.5°	6062.8
5°	5977.4
7.5°	5861.7
10°	5630.4
12.5°	5370.6
15°	5046.3
17.5°	4657.5
20°	4210.0
22.5°	3739.7
25°	3258.0
27.5°	2717.5
30°	2182.7
32.5°	1604.3
35°	953.9
37.5°	508.2
40°	286.4
42.5°	157.4
45°	85.3
47.5°	43.6
50°	36.0
52.5°	32.2
55°	28.4
57.5°	26.5
60°	24.7
62.5°	20.9
65°	19.0
67.5°	15.2
70°	15.2
72.5°	13.3
75°	13.3
77.5°	11.4
80°	11.4
82.5°	9.5
85°	9.5
87.5°	5.7
90°	0.0

(END OF REPORT)