

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364960

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI
Description: VANDAL RESISTANT OPEN, SPECULAR CLEAR REFLECTOR, 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5167.0 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364960

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI

Luminous Intensity Polar Plot





TEST NUMBER: P364960

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	87	84	83
4	99	92	87	83	97	91	86	82	88	84	81	87	83	80	85	82	79	78
5	94	86	81	77	93	85	80	76	84	79	76	82	78	75	81	77	75	73
6	90	81	76	72	88	81	75	72	79	75	71	78	74	71	77	73	70	69
7	86	77	71	67	84	76	71	67	75	70	67	74	70	66	73	69	66	65
8	82	73	67	63	81	72	67	63	71	66	63	70	66	63	69	65	62	61
9	78	69	64	60	77	69	63	60	68	63	60	67	62	59	66	62	59	58
10	75	66	60	57	74	65	60	56	64	60	56	64	59	56	63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	204029
5°	199346
10°	184293
15°	162968
20°	138923
25°	115562
30°	89633
35°	46557
40°	21623
45°	8170
50°	1798
55°	252
60°	98
65°	116
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P364960

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	673.7	13.0
10°-20°	1602.0	31.0
20°-30°	1746.0	33.8
30°-40°	944.1	18.3
40°-50°	190.7	3.7
50°-60°	9.0	0.2
60°-70°	1.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4021.6	77.8
0°-40°	4965.7	96.1
0°-60°	5165.5	100.0
0°-90°	5167.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5167.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7469	
5°	7270	674
15°	5763	1602
25°	3834	1746
35°	1396	944
45°	212	191
55°	5	9
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P364960

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7469.4
2.5°	7420.0
5°	7270.2
7.5°	7000.5
10°	6644.4
12.5°	6219.5
15°	5762.9
17.5°	5290.5
20°	4779.2
22.5°	4297.9
25°	3834.3
27.5°	3368.9
30°	2841.8
32.5°	2138.4
35°	1396.2
37.5°	932.6
40°	606.4
42.5°	373.7
45°	211.5
47.5°	105.8
50°	42.3
52.5°	10.6
55°	5.3
57.5°	3.5
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)