

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365002

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365002
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC, CLEAR 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5569.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365002

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P365002

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	81	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	59	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215613
5°	211235
10°	195005
15°	173344
20°	147934
25°	123947
30°	97143
35°	51219
40°	23930
45°	9414
50°	2460
55°	667
60°	437
65°	388
70°	319
75°	422
80°	315
85°	627



TEST NUMBER: P365002

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	712.9	12.8
10°-20°	1702.3	30.6
20°-30°	1872.5	33.6
30°-40°	1033.6	18.6
40°-50°	218.1	3.9
50°-60°	17.8	0.3
60°-70°	5.4	0.1
70°-80°	4.5	0.1
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4287.7	77.0
0°-40°	5321.3	95.6
0°-60°	5557.2	99.8
0°-90°	5569.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5569.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7894	
5°	7704	713
15°	6130	1702
25°	4112	1872
35°	1536	1034
45°	244	218
55°	14	18
65°	6	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P365002

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BV

CANDELA DISTRIBUTION (FULL):

0°	
0°	7893.5
2.5°	7833.6
5°	7703.8
7.5°	7410.1
10°	7030.6
12.5°	6595.2
15°	6129.8
17.5°	5630.5
20°	5089.2
22.5°	4597.9
25°	4112.5
27.5°	3619.2
30°	3079.9
32.5°	2344.9
35°	1536.0
37.5°	1020.6
40°	671.1
42.5°	423.4
45°	243.7
47.5°	127.8
50°	57.9
52.5°	24.0
55°	14.0
57.5°	10.0
60°	8.0
62.5°	6.0
65°	6.0
67.5°	4.0
70°	4.0
72.5°	6.0
75°	4.0
77.5°	4.0
80°	2.0
82.5°	2.0
85°	2.0
87.5°	2.0
90°	0.0

(END OF REPORT)