

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365671

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-MW-BTR81**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P365671  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-MW-BTR81  
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, MATTE WHITE REFLECTOR,  
BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2774.9 lumens  
Efficiency: N/A  
Efficacy: 50.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.19  
Luminous Opening: Circular (Dia: 0.44' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P365671

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-MW-BTR81

### Luminous Intensity Polar Plot





TEST NUMBER: P365671

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-MW-BTR81

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	101	98	96		97	95	93		93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82		87	84	80		84	81	79	77
3	95	86	79	73	93	84	78	73	81	76	71		79	74	70		76	72	69	67
4	88	77	70	64	86	76	69	64	74	68	63		72	66	62		70	65	61	59
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	51	74	63	56	50	62	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	51	45	57	50	45		55	49	45		54	49	44	43
8	66	54	46	41	65	54	46	41	52	46	41		51	45	41		50	45	40	39
9	62	50	43	38	61	50	42	37	48	42	37		47	41	37		46	41	37	35
10	59	47	39	34	58	46	39	34	45	39	34		44	38	34		43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100479
5°	102638
10°	105235
15°	104676
20°	101959
25°	97222
30°	90368
35°	82288
40°	73327
45°	63379
50°	52822
55°	43792
60°	36603
65°	31055
70°	26566
75°	21938
80°	17442
85°	13062



TEST NUMBER: P365671

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-MW-BTR81

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.0	4.9
10°-20°	396.7	14.3
20°-30°	564.2	20.3
30°-40°	586.6	21.1
40°-50°	482.1	17.4
50°-60°	318.4	11.5
60°-70°	184.4	6.6
70°-80°	85.9	3.1
80°-90°	19.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1097.8	39.6
0°-40°	1684.4	60.7
0°-60°	2484.9	89.5
0°-90°	2774.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2774.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1403	
5°	1428	137
15°	1412	397
25°	1231	564
35°	941	587
45°	626	482
55°	351	318
65°	183	184
75°	79	86
85°	16	20
90°	0	



TEST NUMBER: P365671

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8040-F6LBXVM1-MW-BTR81

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1403.3
2.5°	1412.1
5°	1428.0
7.5°	1443.9
10°	1447.4
12.5°	1431.5
15°	1412.1
17.5°	1382.2
20°	1338.1
22.5°	1288.7
25°	1230.6
27.5°	1168.9
30°	1093.0
32.5°	1019.0
35°	941.4
37.5°	860.3
40°	784.5
42.5°	703.4
45°	625.9
47.5°	548.3
50°	474.2
52.5°	412.5
55°	350.8
57.5°	299.7
60°	255.6
62.5°	216.8
65°	183.3
67.5°	155.1
70°	126.9
72.5°	102.3
75°	79.3
77.5°	59.9
80°	42.3
82.5°	28.2
85°	15.9
87.5°	7.1
90°	0.0

(END OF REPORT)