

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365003

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BW
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS ACRYLIC OPAL SMOOTH, CLEAR 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4119.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365003

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BW

Luminous Intensity Polar Plot





TEST NUMBER: P365003

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	78	96	89	83	77	85	80	75		82	78	74		79	75	72	70
3	90	80	71	65	88	78	70	64	75	69	63		72	67	62		70	65	61	59
4	83	71	62	55	80	69	61	55	67	59	54		64	58	53		62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46		58	51	46		56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41		52	45	40		51	45	40	38
7	65	51	43	36	63	51	42	36	49	41	36		48	41	36		46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32		44	37	32		42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29		40	34	29		39	33	29	27
10	53	40	32	26	52	39	32	26	38	31	26		37	31	26		36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40159
5°	40148
10°	39724
15°	39486
20°	39367
25°	38952
30°	38685
35°	38301
40°	37751
45°	37347
50°	36754
55°	36055
60°	34920
65°	33441
70°	31267
75°	27830
80°	22305
85°	13759



TEST NUMBER: P365003

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.7	3.4
10°-20°	394.8	9.6
20°-30°	596.7	14.5
30°-40°	717.6	17.4
40°-50°	745.3	18.1
50°-60°	675.7	16.4
60°-70°	511.5	12.4
70°-80°	279.3	6.8
80°-90°	59.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1130.2	27.4
0°-40°	1847.7	44.9
0°-60°	3268.8	79.4
0°-90°	4119.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4119.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1470	
5°	1464	139
15°	1396	395
25°	1292	597
35°	1149	718
45°	967	745
55°	757	676
65°	517	511
75°	264	279
85°	44	59
90°	0	



TEST NUMBER: P365003

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BL89BW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1470.2
2.5°	1464.2
5°	1464.2
7.5°	1452.2
10°	1432.2
12.5°	1422.2
15°	1396.3
17.5°	1376.3
20°	1354.3
22.5°	1328.4
25°	1292.4
27.5°	1260.4
30°	1226.5
32.5°	1188.5
35°	1148.6
37.5°	1102.6
40°	1058.7
42.5°	1014.7
45°	966.8
47.5°	916.9
50°	864.9
52.5°	813.0
55°	757.1
57.5°	699.1
60°	639.2
62.5°	579.3
65°	517.4
67.5°	455.4
70°	391.5
72.5°	327.6
75°	263.7
77.5°	201.8
80°	141.8
82.5°	89.9
85°	43.9
87.5°	14.0
90°	0.0

(END OF REPORT)