

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365005

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR81**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365005
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-25)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR81
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, PATTERN 12 0.156", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4404.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.19
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365005

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR81

Luminous Intensity Polar Plot





TEST NUMBER: P365005

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR81

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	76	73	72
4	91	81	74	69	89	80	73	68	78	72	68		75	71	67		73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	61		69	64	60		68	63	59	58
6	79	68	61	55	77	67	60	55	66	59	55		64	59	54		63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58	53	49	47
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	42		51	46	41		50	45	41	40
10	62	50	43	39	61	50	43	38	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163675
5°	175635
10°	189284
15°	194756
20°	192893
25°	181859
30°	164894
35°	143798
40°	120548
45°	97038
50°	74722
55°	54328
60°	36875
65°	24346
70°	15890
75°	12145
80°	10721
85°	13145



TEST NUMBER: P365005

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR81

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.6	5.4
10°-20°	737.1	16.7
20°-30°	1052.4	23.9
30°-40°	1023.9	23.2
40°-50°	740.6	16.8
50°-60°	397.0	9.0
60°-70°	149.7	3.4
70°-80°	49.2	1.1
80°-90°	15.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2028.1	46.1
0°-40°	3052.0	69.3
0°-60°	4189.6	95.1
0°-90°	4404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4404.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2286	
5°	2444	239
15°	2627	737
25°	2302	1052
35°	1645	1024
45°	958	741
55°	435	397
65°	144	150
75°	44	49
85°	16	16
90°	0	



TEST NUMBER: P365005

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR81

CANDELA DISTRIBUTION (FULL):

	0°
0°	2285.9
2.5°	2351.8
5°	2443.6
7.5°	2543.5
10°	2603.4
12.5°	2629.3
15°	2627.3
17.5°	2591.4
20°	2531.5
22.5°	2435.7
25°	2301.9
27.5°	2158.1
30°	1994.4
32.5°	1826.7
35°	1645.1
37.5°	1461.4
40°	1289.7
42.5°	1114.0
45°	958.3
47.5°	806.6
50°	670.8
52.5°	545.0
55°	435.2
57.5°	341.4
60°	257.5
62.5°	193.7
65°	143.7
67.5°	103.8
70°	75.9
72.5°	57.9
75°	43.9
77.5°	33.9
80°	26.0
82.5°	20.0
85°	16.0
87.5°	8.0
90°	0.0

(END OF REPORT)