

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365009

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR86
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM POLYCARBONATE, CLEAR 0.250", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4344.9 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365009

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR86

Luminous Intensity Polar Plot





TEST NUMBER: P365009

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	487673
5°	476555
10°	439336
15°	389119
20°	329438
25°	260997
30°	183414
35°	76387
40°	26209
45°	6997
50°	3854
55°	3595
60°	3294
65°	3253
70°	3224
75°	3707
80°	4742
85°	7887



TEST NUMBER: P365009

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	614.4	14.1
10°-20°	1456.3	33.5
20°-30°	1495.0	34.4
30°-40°	633.1	14.6
40°-50°	77.8	1.8
50°-60°	25.8	0.6
60°-70°	19.0	0.4
70°-80°	14.7	0.3
80°-90°	8.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3565.7	82.1
0°-40°	4198.7	96.6
0°-60°	4302.3	99.0
0°-90°	4344.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4344.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6811	
5°	6630	614
15°	5249	1456
25°	3304	1495
35°	874	633
45°	69	78
55°	29	26
65°	19	19
75°	13	15
85°	10	9
90°	0	



TEST NUMBER: P365009

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR86

CANDELA DISTRIBUTION (FULL):

0°	
0°	6810.9
2.5°	6766.7
5°	6630.3
7.5°	6396.0
10°	6042.6
12.5°	5666.1
15°	5249.3
17.5°	4801.8
20°	4323.5
22.5°	3814.6
25°	3303.6
27.5°	2775.4
30°	2218.4
32.5°	1563.5
35°	873.9
37.5°	501.3
40°	280.4
42.5°	147.9
45°	69.1
47.5°	40.3
50°	34.6
52.5°	30.7
55°	28.8
57.5°	26.9
60°	23.0
62.5°	21.1
65°	19.2
67.5°	17.3
70°	15.4
72.5°	15.4
75°	13.4
77.5°	13.4
80°	11.5
82.5°	11.5
85°	9.6
87.5°	5.8
90°	0.0

(END OF REPORT)