

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364963

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL86**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P364963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-43)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL86
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,
BOTTOM LENS POLYCARBONATE, CLEAR 0.250", 5000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4713.0 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.82
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 55.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P364963

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL86

Luminous Intensity Polar Plot





TEST NUMBER: P364963

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL86

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	72	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	58	56	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181330
5°	177882
10°	164270
15°	146383
20°	125011
25°	104989
30°	82420
35°	42709
40°	20396
45°	8027
50°	2112
55°	591
60°	388
65°	343
70°	288
75°	380
80°	283
85°	564



TEST NUMBER: P364963

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL86

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	601.6	12.8
10°-20°	1438.6	30.5
20°-30°	1588.4	33.7
30°-40°	874.0	18.5
40°-50°	184.7	3.9
50°-60°	15.6	0.3
60°-70°	4.8	0.1
70°-80°	3.5	0.1
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3628.6	77.0
0°-40°	4502.6	95.5
0°-60°	4703.0	99.8
0°-90°	4713.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4713.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6638	
5°	6487	602
15°	5176	1439
25°	3484	1588
35°	1281	874
45°	208	185
55°	12	16
65°	5	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P364963

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL86

CANDELA DISTRIBUTION (FULL):

0°	
0°	6638.4
2.5°	6634.8
5°	6487.4
7.5°	6260.0
10°	5922.5
12.5°	5586.7
15°	5176.4
17.5°	4758.9
20°	4300.6
22.5°	3899.2
25°	3483.5
27.5°	3082.0
30°	2613.1
32.5°	1994.9
35°	1280.8
37.5°	863.3
40°	572.0
42.5°	357.1
45°	207.8
47.5°	106.6
50°	49.7
52.5°	21.3
55°	12.4
57.5°	8.9
60°	7.1
62.5°	5.3
65°	5.3
67.5°	3.6
70°	3.6
72.5°	5.3
75°	3.6
77.5°	1.8
80°	1.8
82.5°	1.8
85°	1.8
87.5°	1.8
90°	0.0

(END OF REPORT)