

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365012

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365012
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-22)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM TRIM RING, SPECULAR CLEAR REFLECTOR, BOTTOM TRIM ACRYLIC, CLEAR 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4736.1 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365012

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR89BV

Luminous Intensity Polar Plot





TEST NUMBER: P365012

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	68	66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	530677
5°	518351
10°	476423
15°	424003
20°	359140
25°	285591
30°	200785
35°	83791
40°	28938
45°	7483
50°	3787
55°	3495
60°	3437
65°	3388
70°	3350
75°	4426
80°	4948
85°	8215



TEST NUMBER: P365012

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	667.6	14.1
10°-20°	1584.5	33.5
20°-30°	1634.9	34.5
30°-40°	695.4	14.7
40°-50°	83.5	1.8
50°-60°	25.3	0.5
60°-70°	19.8	0.4
70°-80°	15.9	0.3
80°-90°	9.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3887.1	82.1
0°-40°	4582.5	96.8
0°-60°	4691.2	99.1
0°-90°	4736.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4736.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7412	
5°	7212	668
15°	5720	1584
25°	3615	1635
35°	959	695
45°	74	83
55°	28	25
65°	20	20
75°	16	16
85°	10	9
90°	0	



TEST NUMBER: P365012

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-LI-BTR89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	7411.5
2.5°	7363.5
5°	7211.8
7.5°	6948.1
10°	6552.7
12.5°	6163.2
15°	5719.9
17.5°	5220.6
20°	4713.3
22.5°	4184.1
25°	3614.9
27.5°	3027.7
30°	2428.5
32.5°	1721.6
35°	958.6
37.5°	551.2
40°	309.6
42.5°	159.8
45°	73.9
47.5°	39.9
50°	34.0
52.5°	30.0
55°	28.0
57.5°	26.0
60°	24.0
62.5°	22.0
65°	20.0
67.5°	18.0
70°	16.0
72.5°	16.0
75°	16.0
77.5°	14.0
80°	12.0
82.5°	12.0
85°	10.0
87.5°	6.0
90°	0.0

(END OF REPORT)