

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P365722

Luminaire Tested: **FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89BV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P365722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-34)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89BV
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, MATTE WHITE REFLECTOR, BOTTOM LENS ACRYLIC, CLEAR 0.125", 6000LM
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4840.0 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.95
Luminous Opening: Circular (Dia: 0.71' x H: 0')
CIE Type: Direct


Input Watts (W): 58.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P365722

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89BV

Luminous Intensity Polar Plot





TEST NUMBER: P365722

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89BV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	52	48	58	52	47		57	51	47		56	51	47	45
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	64	52	46	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107139
5°	104754
10°	99869
15°	93233
20°	87007
25°	80215
30°	68318
35°	51969
40°	38047
45°	28945
50°	23521
55°	20649
60°	18558
65°	16404
70°	13880
75°	10965
80°	7551
85°	3134



TEST NUMBER: P365722

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89BV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.0	7.4
10°-20°	926.1	19.1
20°-30°	1206.8	24.9
30°-40°	982.5	20.3
40°-50°	592.5	12.2
50°-60°	392.8	8.1
60°-70°	252.1	5.2
70°-80°	112.3	2.3
80°-90°	16.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2490.9	51.5
0°-40°	3473.4	71.8
0°-60°	4458.7	92.1
0°-90°	4840.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4840.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3922	
5°	3820	358
15°	3297	926
25°	2662	1207
35°	1558	983
45°	749	593
55°	434	393
65°	254	252
75°	104	112
85°	10	17
90°	0	



TEST NUMBER: P365722

CATALOG NUMBER: FLD6BX60D010TE-FEU6B67-8030-F6LBXVM1-MW-BL89BV

CANDELA DISTRIBUTION (FULL):

	0°
0°	3922.3
2.5°	3902.3
5°	3820.4
7.5°	3726.5
10°	3600.6
12.5°	3450.8
15°	3296.9
17.5°	3147.0
20°	2993.2
22.5°	2839.3
25°	2661.5
27.5°	2443.7
30°	2166.0
32.5°	1876.2
35°	1558.5
37.5°	1292.8
40°	1067.0
42.5°	889.2
45°	749.3
47.5°	639.4
50°	553.5
52.5°	491.5
55°	433.6
57.5°	387.6
60°	339.7
62.5°	295.7
65°	253.8
67.5°	213.8
70°	173.8
72.5°	137.9
75°	103.9
77.5°	73.9
80°	48.0
82.5°	26.0
85°	10.0
87.5°	2.0
90°	0.0

(END OF REPORT)