

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P364966

Luminaire Tested: **FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL89BV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P364966  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-544-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL89BV  
Description: VANDAL RESISTANT ENCLOSED BOTTOM LENS, SPECULAR CLEAR REFLECTOR,  
BOTTOM LENS ACRYLIC, CLEAR 0.125", 5000LM  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5034.0 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82  
Luminous Opening: Circular (Dia: 0.71' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P364966

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL89BV

### Luminous Intensity Polar Plot





TEST NUMBER: P364966

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL89BV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	83
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84	81	79	77
5	94	86	81	76	92	85	80	76	83	79	75		82	78	75		80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71		77	73	70		76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66		74	69	66		72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63		70	65	62		69	65	62	61
9	78	69	63	59	77	68	63	59	67	62	59		66	62	59		66	62	59	57
10	74	65	60	56	74	65	60	56	64	59	56		63	59	56		63	59	56	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	194900
5°	190942
10°	176272
15°	156693
20°	133723
25°	112039
30°	87810
35°	46297
40°	21630
45°	8510
50°	2227
55°	600
60°	393
65°	349
70°	288
75°	380
80°	283
85°	564



TEST NUMBER: P364966

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL89BV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	644.5	12.8
10°-20°	1538.8	30.6
20°-30°	1692.6	33.6
30°-40°	934.3	18.6
40°-50°	197.1	3.9
50°-60°	16.1	0.3
60°-70°	4.9	0.1
70°-80°	4.0	0.1
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3875.8	77.0
0°-40°	4810.1	95.6
0°-60°	5023.3	99.8
0°-90°	5034.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5034.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7135	
5°	6964	644
15°	5541	1539
25°	3717	1693
35°	1388	934
45°	220	197
55°	13	16
65°	5	5
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P364966

CATALOG NUMBER: FLD6BX50D010TE-FEU6B35-8050-F6LBXVM1-LI-BL89BV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7135.2
2.5°	7081.0
5°	6963.7
7.5°	6698.3
10°	6355.2
12.5°	5961.6
15°	5541.0
17.5°	5089.6
20°	4600.3
22.5°	4156.2
25°	3717.4
27.5°	3271.5
30°	2784.0
32.5°	2119.6
35°	1388.4
37.5°	922.6
40°	606.6
42.5°	382.8
45°	220.3
47.5°	115.5
50°	52.4
52.5°	21.7
55°	12.6
57.5°	9.0
60°	7.2
62.5°	5.4
65°	5.4
67.5°	3.6
70°	3.6
72.5°	5.4
75°	3.6
77.5°	3.6
80°	1.8
82.5°	1.8
85°	1.8
87.5°	1.8
90°	0.0

(END OF REPORT)